



**Product:** [ECX-1U2U-EXSTR](#)

FX ECX 1U/2U External Strain Relief

### Product Description

ECX-1U2U-EXSTR contains 2 external strain reliefs and 4 screws. This component is used to hold distribution cables to FX ECX 1U/2U Patch Panel Housings.

### Technical Specifications

#### Product Overview

Environmental Space:	Indoor
Suitable Applications:	ECX Patch Panel, cable management

#### Construction

Weight:	0.350 lbs
Height:	2.5 in
Width:	3.500 in
Depth:	1.200 in

#### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

#### Product Material

##### Materials

Description	Material	Color
External strain relief	Steel	Black
Machine screw #2	Stainless Steel	Black

#### Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
UV/ Sunlight Protection:	Yes

#### Related Part Numbers

Related Parts:	ECX Patch Panel 1U/2U
----------------	-----------------------

##### Variants

Item #	Color	UPC
ECX-1U2U-EXSTR	Black	611589224505

#### Product Notes

Packaging:	Parts packaged in a bubble bag
Notes:	Phillips #2 screwdriver is required for installation

#### History

Update and Revision:	Revision Number: 0.51 Revision Date: 11-14-2022
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.