



**Product:** [FACEPLATE TWO PCS FLUSH](#)

KeyConnect (86x86mm) Faceplate, Copper, Flat, Premium Two-piece

### Product Description

KeyConnect (86x86mm) Modular Outlet Faceplate, Copper, Flat, Premium Two-piece

### Technical Specifications

#### Product Overview

Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1205
------------------------	--

#### Physical Characteristics (Overall)

Height:	86 mm
Width:	86 mm
Depth:	14.42 mm
Front Connection:	Flush
Packaging:	Individually packaged in a plastic bag.

#### Connectors

##### Materials

Description	Material
Faceplate	Plastic - PC-ABS, UL94V-0

#### Mechanical Characteristics

Footprint/Type:	KeyConnect
Plug /Jack Compatibility:	RJ45

#### Standards

TIA/EIA Compliance:	ISO/IEC 11801-1:2017
---------------------	----------------------

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes
MII Order #39 (China RoHS):	EUP 50

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL-94V0
------------------	---------

#### Related Part Numbers

Related Parts:	Compatible with UTP KeyConnect and UTP & Shielded REV Connect Multimedia Modules for 10GX, CAT6+ and CAT5E.
----------------	---

#### History

Update and Revision:	Revision Number: 0.44 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.