




Product: [FRD3TYH](#)



Fiber Raceway Slotted Duct 4x4 with Hinged Lid

Product Description

Fiber Raceway Slotted Duct & Hinged Lid, 4x4, 2 meters long

Technical Specifications

Product Overview

Environmental Space:	Indoor
----------------------	--------

Construction

Weight:	7.275 lbs
Height:	4.133 in (104.978 mm)
Width:	4.724 in
Length:	78.740 in

Product Material

Materials

Material
Fire retardant plastic, Halogen free, UL94-VO rated

Related Part Numbers

Variants

Item #	Color	Length
FRD3TYH	Yellow	78.740 in

Product Notes

Notes:	This 100 mm duct is similar to standard duct except that it is slotted to allow optical fibre cord feed off at 150mm intervals and external vision of the duct's contents. It carries up to 400 pigtailed or patch cords (3mm dia) to a depth of 50 mm, without excess stress on them, during removal processes. The duct comes complete with a lid and is made of tough Noryl plastic with a non halogen, fire retardant. It connects to other 100mm duct sections and various bends adapters etc., using either: a standard joiner or a slotless joiner. It is recommended that each outlet slot be fitted with an outlet radius guide, that will guarantee the outgoing radius for every housed optical fibre cord. These are available separately.
--------	--

History

Update and Revision:	Revision Number: 0.72 Revision Date: 03-28-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.