




Product: [FWSHBS04LUW](#)

DuetConnect Hybrid Termination Box



Product Description

DuetConnect HTB 4C/4F LC Quad OS2 Pigtails, Adapters with Shutter, White

Technical Specifications

Physical Characteristics (Overall)

Height:	0.92 in
Width:	3.54 in
Depth:	5.23 in
Front Connection:	Flush
Packaging:	Individually packaged in a box.
Weight:	0.161 lbs

Connectors

Materials

Description	Material	Color	Type
Adapter Sleeve	Zirconia-Ceramic		
Front Fiber Connector Body	Plastic - UL94V-0	Blue	LC Quad
Box Assembly	Plastic - UL94V-0	White	
Front Copper Connector Body	Plastic - UL94V-0	Green	

Construction and Dimensions

Max Capacity:	4 Fibers, 1 LC Quad Adapter
---------------	-----------------------------

Temperature Range

Installation Temperature Range:	-10°C to 60°C
Storage Temperature Range:	-10°C to 75°C

Mechanical Characteristics

Dimensions (WxHxD)

Width	Height	Depth
3.54 in	0.92 in	5.23 in

Standards

UL Rating:	Tested to UL2043 for Plenum spaces
------------	------------------------------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

Product Notes

Included Parts:	(2) 900µm Pigtails, (4) Slim Splice Protection sleeve 25mm, (2) Self-locking cable tie /4.0, (2) TRI-COMBO PAN HD 6-32 MACH. SCREW 1.25 LG.
-----------------	---

History

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.