

Part Number: FX ECX 1U Patch Panel Housing
FX ECX LAN 1U Patch Panel Housing 19" width



Product Description

FiberExpress ECX Patch Panel Housing 1U, holds 2 ECX adapter frames or cassettes

Technical Specifications

Part Number:	ECX-01U
--------------	---------

Product Overview

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

Construction

Weight:	4.440 lbs
Height:	1.732 in
Width:	19.122
Depth:	17.564

Physical Specifications

Max Capacity:	Holds 2 ECX adapter frames or cassettes
---------------	---

Mechanical Characteristics

Termination Type:	Front Sliding Door
-------------------	--------------------

Temperature Range

Operating Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C

Product Material

Materials

Element	Description
Steel	Housing
PC/ABS	Housing
Polycarbonate	Housing

Standards

Telecommunications Standards:	EIA/ECA 310
MII Order #39 (China RoHS):	EUP 50

Additional Notes

Packaging:	Individually packaged in a cardboard box.
Included Parts:	Screws (12-24); Screws (10-32); Tie Wraps; Velcro Straps; Identification Labels; Quick Installation Guides; Strain Reliefs
Related Parts:	FiberExpress ECX Frames, Cassettes and Housing Accessories
Notes:	For more information, please refer to our web site at http://www.belden.com . Installation Guide: PX106483

History

Variants

Item #	Color	UPC
ECX-01U	Black, White	611589224802

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.