



**Product:** [FX Fusion Splicer Kit](#)

**FiberExpress Fusion Splicer Kit**



**Product Description**

FiberExpress Fusion Splicer Kit, FXFSTOSPL

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Indoor termination of fiber cables: Patch panels, Communication outlets, Fiber-to-the-desk, Distribution frames, Direct termination to equipment, Campus, Customer premise, Access network, Fiber cable repair

**Construction**

Weight:	Fusion splicer only: 2.425 lbs Complete fusion splicer kit: 7.2 lbs
---------	---

**Absolute Maximum Ratings**

Power Supply:	Lithium-ion Battery (14.8 V DC, 3400mAh), 100-240V AC charger
---------------	---

**Related Part Numbers**

Included Parts:	Main splicer unit with battery, AC adapter/charger, shoulder strap, cleaning brushes, fiber holders/clamps, spare electrodes, cooling tray, carrying case, user guide CD, keys for lock, screwdriver, tackle box, & a splice holder family 2 (FXFSSHFM2)
Related Parts:	FX Fusion connectors, FiberExpress Fusion Precision Kit. Compatible Splice holder (FXFSSHFM2) required for splicing FX Fusion connectors is sold separately

**Variants**

Item #	Color	UPC
FXFSTOSPL	Black	611589225670

**Product Notes**

Packaging:	The splicer and accessories are individually packaged in a plastic carrying case.
------------	---

**History**

Update and Revision:	Revision Number: 0.190 Revision Date: 11-09-2022
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.