




**Product:** [FXWSKCSLYNB25WO](#)



Faceplates and Panels - KeyConnect LC Duplex Module OS2

## Product Description

FX Workstation KeyConnect Adapter, OS2, LC Duplex Hybrid Keyed, Orange Adapter, White Holder

## Technical Specifications

### Product Overview

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
------------------------	---

### Physical Characteristics (Overall)

Height:	0.917 in
Width:	0.685 in
Depth:	1.149 in
Packaging:	packaged 25 units per bag

### Connectors

#### Materials

Description	Material	Color	Type
Holder	Plastic - UL94V-0	White	KeyConnect
Adapter	Plastic - UL94V-0	Orange	Keyed LC Duplex

### Temperature Range

Installation Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C
Operating Temperature Range:	-10°C to +60°C

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

### Related Part Numbers

Related Parts:	Compatible KeyConnect-style Faceplate and Patch Panel
----------------	---

### Product Notes

Included Parts:	Dust Caps
-----------------	-----------

### History

Update and Revision:	Revision Number: 0.4 Revision Date: 01-17-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.