



Product: [L-SHAPED MOUNT ANGELS E-SERIES](#)

EDAP60xx - Series



Product Description

Pair of L-Shaped Mounting Angles for E-series.

Technical Specifications

Application

Suitable Applications:	By mounting the angels on the inside of a 19" cabinet, they provide support to servers or switch boxes. Load capacity of one pair is 100 kg.
Environmental Space:	Indoor

Construction and Dimensions

Height:	88 mm
Width:	70 mm

Mechanical Characteristics

Load Capacity - Static:	100 kg of one pair
-------------------------	--------------------

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Related Part Numbers

Variants

Item #	Depth	Application: Min. cabinet depth	Colour
EDAP6031	380 mm	E-Series Cabinets, 600 mm depths.	Gray
EDAP6032	380 mm	E-Series Cabinets, 600 mm depths.	Black
EDAP6041	480 mm	E-Series Cabinets, 600 mm depths.	Gray
EDAP6042	480 mm	E-Series Cabinets, 600 mm depths.	Black
EDAP6051	580 mm	E-Series Cabinets, 800 mm depths.	Gray
EDAP6052	580 mm	E-Series Cabinets, 800 mm depths.	Black
EDAP6061	680 mm	E-Series Cabinets, 900 mm depths.	Gray
EDAP6062	680 mm	E-Series Cabinets, 900 mm depths.	Black
EDAP6071	780 mm	E-Series Cabinets, 1000 mm depths.	Gray
EDAP6072	780 mm	E-Series Cabinets, 1000 mm depths.	Black

Update and Revision:	Revision Number: 0.51 Revision Date: 01-08-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.