



**Product:** [KEYCONNECT 6-PORT MEDIA BOX](#)



## 6-Port KeyConnect Termination Media Box

### Product Description

KeyConnect 6 Port Media Box is available in several colors.

### Technical Specifications

#### Physical Characteristics (Overall)

Height:	1.06 m
Width:	3.32
Depth:	4.87
Front Connection:	Flush
Packaging:	Individually packaged in a box.
Weight:	0.2 kg

#### Connectors

##### Materials

Material
Plastic

#### Temperature Range

Installation Temperature Range:	-10 to 60°C
Storage Temperature Range:	-10 to 75°C

#### Mechanical Characteristics

Footprint/Type:	KeyConnect
-----------------	------------

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2002/95/EC (RoHS):	Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	UL2043 Air Handling Spaces
------------------	----------------------------

#### Related Part Numbers

Related Parts:	Compatible with KeyConnect-style Modular jacks10GX, CAT6+ and CAT5E.
----------------	--

##### Variants

Item #	Color	Port Count
AX106512-BK	Black	6 Port
AX105816	Brown	6 Port
AX106512-EW	Electric White	6 Port

#### Product Notes

Included Parts:	(4) #6-32 mounting screws, (2) #4-40 cover std screws, (1) zip tie, (2) label, (2) label, window, (2) 2 sided adhesive
-----------------	--

Notes:	suitable for installation in Plenum/Air Handling Spaces per UL 2043
--------	---

## History

Update and Revision:	Revision Number: 0.67 Revision Date: 03-04-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.