


Product: [MTM2800-PSU120](#) 

MAMMUTHUS PSU for MTS2848TF-4X-E Switch



Product Description

AC/DC 120W PSU; Input 100-240V/2.0A; Output 12V/10A; Without PoE support

Technical Specifications

Product description

Type:	MTM2800-PSU120
Name:	MTM2800-PSU120
Description:	AC/DC 120W PSU; Input 100-240V/2.0A; Output 12V/10A; Without PoE support
Part Number:	942999840

Power requirements

Current consumption:	1A (220V), 2A (110V)
Input frequency:	50-60HZ
Nominal power of voltage supply:	120W (220V/110V)
Operating Voltage:	100-240VAC
Activation Current:	typ. 40A at 220VAC and cold start

Diagnostics features

Diagnostic functions:	LEDs (PWR) at basic device
-----------------------	----------------------------

Ambient conditions

Operating temperature:	-10-+55 °C
------------------------	------------

Approvals

FCC:	CE/FCC Compliant
China Network Access Certificate:	Compliant
CCC:	Compliant
Common Criteria:	EAL 2+
RoHS Compliant:	RoHS(EU 2015/863) and RoHS(GB/T26572-2011) compliant

Scope of delivery and accessories

Scope of delivery:	PSU module
--------------------	------------

History

Update and Revision:	Revision Number: 0.13 Revision Date: 09-07-2023
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.