




Product: [Lacing/PDU Mounting Panels](#)

Vertical Lacing/PDU Mounting Panels

Product Description

Belden Cabinet Line Vertical Lacing/PDU Mounting Panels

Technical Drawing



Technical Specifications

Application

| | |
|------------------------|---|
| Product Overview: | Manager panels are available in 3.5"W and 7.0"W. Mounts on rail struts for depth adjustability. Panels can be mounted side by side to create manager surface. Tool-Less PDU Mounting. Lacing of cable bundles. Attachment of Ring Managers. Attachment of Slack Management Spools. Attachment of Quick-mount base |
| Benefits: | Can be factory installed if ordered in conjunction with a cabinet. |
| Features: | Mounts on rail struts for depth adjustability, Panels can be mounted side by side to create manager surface, Tool-less PDU mounting, Lacing of cable bundles, Attachment of slack management spools, Attachment of quick mount base |
| Product Specification: | *Lacing/PDU Mounting panels are not included with cabinets or PDU's and need to be ordered separately. |
| Environmental Space: | Indoor |

Mechanical Characteristics

| | |
|-----------|----------|
| Mounting: | Vertical |
|-----------|----------|

Environmental and Overall Characteristics

| | |
|-----------|-------|
| Material: | Steel |
|-----------|-------|

Related Part Numbers

Variants

| Item Part # | Description | Color | Width | Cabinet Application |
|-------------|---|-------|--------|---------------------|
| HNVMPO14501 | Vertical Lacing/PDU Mounting Panel, 45U | Black | 3.5 in | XHN Series |
| HNVMPO14502 | Vertical Lacing/PDU Mounting Panel, 45U | White | 3.5 in | XHN Series |

| | | | | |
|------------|---|-------|--------|---|
| HVMP014201 | Vertical Lacing/PDU Mounting Panel, 42U | Black | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP014202 | Vertical Lacing/PDU Mounting Panel, 42U | White | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP014501 | Vertical Lacing/PDU Mounting Panel, 45U | Black | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP014502 | Vertical Lacing/PDU Mounting Panel, 45U | White | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP014801 | Vertical Lacing/PDU Mounting Panel, 48U | Black | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP014802 | Vertical Lacing/PDU Mounting Panel, 48U | White | 3.5 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024201 | Vertical Lacing/PDU Mounting Panel, 42U | Black | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024202 | Vertical Lacing/PDU Mounting Panel, 42U | White | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024501 | Vertical Lacing/PDU Mounting Panel, 45U | Black | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024501 | Vertical Lacing/PDU Mounting Panel, 45U | Black | 7.0 in | XHN Series |
| HVMP024502 | Vertical Lacing/PDU Mounting Panel, 45U | White | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024502 | Vertical Lacing/PDU Mounting Panel, 45U | White | 7.0 in | XHN Series |
| HVMP024801 | Vertical Lacing/PDU Mounting Panel, 48U | Black | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |
| HVMP024802 | Vertical Lacing/PDU Mounting Panel, 48U | White | 7.0 in | XHM Series XHS Series XHMS Series XHSN Series XHSS Series |

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.154 Revision Date: 04-08-2022 |
|----------------------|--|

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.