

**Product:** [PROVIZE Planner Professional](#) 

Intent-Based Network Planning and Configuration

**Provize**

**Product Description**

Part of Belden's PROVIZE Planning and Management Suite, PROVIZE Planner Professional simplifies network planning and configuration with an advanced feature set. PROVIZE Planner allows users to design networks before buying equipment, saving time and resources. - Easy-to-use with an intuitive interface and drag-and-drop network design capabilities. - Intent-based network planning and configuration through automatic translation of user intents into configurations. - Automatic bill of materials (BOM) generation that identifies relevant equipment based on users' defined network topologies.

**Technical Specifications**

**Product description**

Part Number:	942338002
License:	Paid Version

**Configuration features**

Configuration functions:	Topology Planning, Location Setting, BOM Creation, Redundancy (MRP), Automatic VLAN Configuration, IPv4 Configuration, CLI Template and Template Stacks Configuration, CLI Configuration Export
--------------------------	---

**Diagnostics features**

Modules and components:	Intent-based network planning and configuration through automatic translation of user intents and configurations with an advanced feature set
-------------------------	---

**Software**

Operating system:	Windows 10 (64-Bit) Windows 11 (64-Bit)
Browser:	Windows Application

**Hardware**

Processor:	x86 compatible 64 bit CPU with 4 cores
Hard disk space:	1GB free
RAM:	16 GB
Network:	Ethernet network with TCP/IP protocol stack. Supports IPv4 and IPv6.

**IIT.Protocols**

Supported protocols:	HTTPS, HiDiscovery v2
----------------------	-----------------------

**Language Support**

Menus and dialogs:	English German
--------------------	----------------

**Scope of delivery and accessories**

Scope of delivery:	Software download + Access to functionality under licensing model. License can be purchased via partner.
--------------------	--

**Further Instructions**

Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>
---------------	---

**History**

Update and Revision:	Revision Number: 0.22 Revision Date: 04-22-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.