

Product: [PROVIZE Explorer](#) 

Save Time with Efficient Device Commissioning

Provize

Product Description

PROVIZE Explorer simplifies device commissioning. The software detects devices that have not yet been commissioned and supports configuration of management IP addresses and credentials. - Access Hirschmann interface without installing Java libraries on user's PCs; Simplify initial configuration of IP addresses and credentials via easy-to-use software; Enhance security by verifying device security certificates and enabling the configuration of initial security device settings.

Technical Specifications

Product description

Part Number:	942340001
License:	Free Version

Configuration features

Configuration functions:	Basic Commissioning
--------------------------	---------------------

Diagnostics features

Modules and components:	Discovery and commissioning
-------------------------	-----------------------------

Software

Operating system:	Windows 10 (64-Bit) Windows 11 (64-Bit)
Browser:	Windows Application

Hardware

Processor:	x86 compatible 64 bit CPU with 4 cores
Hard disk space:	1GB free
RAM:	16 GB
Network:	Ethernet network with TCP/IP protocol stack. Supports IPv4 and IPv6.

IIT.Protocols

Supported protocols:	HTTPS, HiDiscovery v2
----------------------	-----------------------

Language Support

Menus and dialogs:	English German
--------------------	----------------

Scope of delivery and accessories

Scope of delivery:	Software download + Access to functionality under licensing model
--------------------	---

Further Instructions

Certificates:	https://www.doc.hirschmann.com/certificates.html
Software Download:	https://hirschmann-support.belden.com/en-US/downloads

History

Update and Revision:	Revision Number: 0.44 Revision Date: 04-22-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.