



Product: [SHELF A-SERIES CABINET](#)



Product Description

Technical Specifications

Application

Environmental Space:	Indoor
----------------------	--------

Mechanical Characteristics

Load Capacity - Static:	90 kg
-------------------------	-------

Environmental and Overall Characteristics

Finish:	Powder Coated
Material:	Steel

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Related Part Numbers

Variants

Item #	Depth	Color	Application
ADAP5261	350 mm	Gray	Free standing A-Series Cabinets, 600 mm depths.
ADAP5262	350 mm	Black	Free standing A-Series Cabinets, 600 mm depths.
ADAP5281	550 mm	Gray	Free standing A-Series Cabinets, 800 mm depths.
ADAP5282	550 mm	Black	Free standing A-Series Cabinets, 800 mm depths.
ADAP5291	620 mm	Gray	Free standing A-Series Cabinets, 900 mm depths.
ADAP5292	620 mm	Black	Free standing A-Series Cabinets, 900 mm depths.
ADAP5211	720 mm	Gray	Free standing A-Series Cabinets, 1000 mm depths.
ADAP5212	720 mm	Black	Free standing A-Series Cabinets, 1000 mm depths.
ADAP5221	920 mm	Gray	Free standing A-Series Cabinets, 1200 mm depths.
ADAP5222	920 mm	Black	Free standing A-Series Cabinets, 1200 mm depths.

Update and Revision:	Revision Number: 0.46 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.