



Product: [REVConnect Universal Termination Tool](#)

REVConnect Universal Handheld Termination Tool

Product Description

REVConnect Universal Termination Tool for use with REVConnect core.

Technical Specifications

Product Overview

Suitable Applications:	To terminate REVConnect Jacks and Plugs
------------------------	---

Physical Characteristics (Overall)

Width:	117.348 mm
Weight:	0.295 kg

Connectors

Materials

Description	Material	Color
Frame	Aluminum	
Handle grip	Plastic	Black
Blade Block	Steel	
Blades & Knives	Steel	
Press Head	Nickel plated zinc alloy diecast	

Temperature Range

Installation Temperature Range:	-10°C To +50°C
Storage Temperature Range:	-40°C To +60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
-----------------	------------

Termination Interface

Connection	Durabilities
Blades	20000
Handle	40000

Dimensions (WxHxD)

Length	Width	Height
34.290 mm	117.348 mm	150.114 mm

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes

Related Part Numbers

Variants

Item #	Color	UPC
--------	-------	-----

History

Update and Revision:	Revision Number: 0.57 Revision Date: 03-04-2023
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.