



Product: [WireNet UTP CAT6 Jack](#)

WN UTP CAT6 Jack



Product Description

WireNet unshielded CAT6 Jack

Technical Specifications

Physical Characteristics (Overall)

Packaging:	Individually packaged in a sealed plastic bag.
------------	--

Temperature Range

Operating Temperature Range:	-20°C to +60°C
------------------------------	----------------

Mechanical Characteristics

Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	Mated Connection
Termination Rear Connection Durability:	20 cycles

Standards

Data Category:	Category 6
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; TIA 568.2-D

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes

Related Part Numbers

Related Parts:	WireNet Patch Cords (CU-LP....) , WireNet Panel (NN-UNIV-E) or KeyConnect empty panels (AX....)
----------------	---

Variants

Item #	Color	Packaging
CU-JU6BK	Black	Individually packaged in a sealed plastic bag.
CU-JU6EW	White	Individually packaged in a sealed plastic bag.

Product Notes

Notes:	Insulation O.D. Range = 0.90 to 1.6 mm, Cable Jacket O.D. Max = 9.2 mm
--------	--

History

Update and Revision:	Revision Number: 0.39 Revision Date: 09-26-2023
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.