

## ECX-1U2U-EXSTR Connectivity Accessories - FX ECX 1U2U EXTERNAL STRAIN RELIEF



For more Information  
please call

1-800-Belden1

### General Description:

ECX-1U2U-EXSTR contains 2 external strain reliefs and 4 screws. This component is used to hold distribution cables to FX ECX 1U/2U Patch Panel Housings.

### Usage (Overall)

**Suitable Applications:** ECX Patch Panel, cable management

**Related Parts:** ECX Patch Panel 1U/2U

### Physical Characteristics (Connectivity)

#### Dimensions

##### Dimensions:

Height (mm)	Width (mm)	Depth (mm)
63.500	88.900	30.480

#### Materials

##### Materials:

Description	Material	Color
External strain relief	Steel	Black
Machine screw #2	Stainless Steel	Black

#### Weight

**Weight:** 0.159 kg

#### Packaging

**Packaging:** parts packaged in a bubble bag

### Mechanical Characteristics (Connectivity)

**Storage Temperature Range:** -40°C To +70°C

**Installation Temperature Range:** -10°C To +60°C

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

**EU Directive 2011/65/EU (ROHS II):** Yes

**EU RoHS Compliance Date (mm/dd/yyyy):** 01/01/2013

#### Suitability

**Sunlight Resistance:** Yes

### Notes (Overall)

**Notes:** Phillips #2 screwdriver is required for installation.

#### Product Family

##### Part Number List:

Description	Item Number
FX ECX Patch Panel Housing 1U	ECX-01U
FX ECX Patch Panel Housing 2U	ECX-02U
FX ECX Patch Panel Housing 4U	ECX-04U

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
ECX-1U2U-EXSTR	1 EA	0.400 LB			FX ECX EXTERNAL STRAIN RELIEF

METRIC MEASUREMENT VERSION

## ECX-1U2U-EXSTR Connectivity Accessories - FX ECX 1U2U EXTERNAL STRAIN RELIEF

Revision Number: 0    Revision Date: 05-30-2017

© 2020 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.