

Compliance Overview NetModule Products

Legend:

- available
- not necessary
- in progress

Country Type Approvals

Vertical

Material

Europe ¹	UK	FCC	UL Safety	PTCRB	AT&T	Australia & New Zealand	E-Mark ECE R10	Fire Safety ECE R118	Onboard EN50155	Trackside EN50121-2	Fire Safety EN45545-2	Fire Safety NFPA130	RoHS	REACH
---------------------	----	-----	-----------	-------	------	-------------------------	----------------	----------------------	-----------------	---------------------	-----------------------	---------------------	------	-------

IIoT and Industrial Router	NB800-LjWWtScSu-SGVise	•	•	•	•	•	•		•	•		•	•	
	NB800-LScSu-G	•	•	•	•				•	•		•	•	
	NB800-LSu-G	•	•	•	•				•	•		•	•	
	NB800-LSu-GE	•	•	•	•				•	•		•	•	
	NB800-LWWtScSu-G	•	•	•	•				•	•		•	•	
	NB800-LWWtSu-G	•	•	•	•				•	•		•	•	
	NB800-LWWtSu-GE	•	•	•	•				•	•		•	•	
	NB800-LWWtSu2Cm-G	•	•	•	•				•	•		•	•	
	NB800-LWWtSu2Cm-GE	•	•	•	•				•	•		•	•	
	NB800-LWWtSu2Cn-G	•	•	•	•				•	•	•	•	•	
	NB800-Usu	•	•		•				•	•			•	•
	NB1601-Gr	•	•										•	•
	NB1601-LjWWtSc-SGVise	•	•	•	•	•	•	•	•				•	•
	NB1601-LSc	•	•	•	•								•	•
	NB1601-LSc-G	•	•	•	•								•	•
	NB1601-LWWtSc-G	•	•	•	•								•	•
	NB1601-R	•	•	•	•	⦿		⦿					•	•
	NB1800-2Wac	•	•	•	⦿		⦿		⦿				•	•
	NB1800-Lp-G	•	•	•	⦿								•	•
	NB1800-LpWac-G	•	•	•	⦿								•	•
	NB1800-Lwac	•	•		⦿								•	•
	NB1800-LWac-G	•	•		⦿								•	•
	NB1800-N-G	•	•		⦿								•	•
	NB1800-NWac-G	•	•		⦿								•	•
	NB1810-L4E-G	•	•		⦿								•	•
	NB1810-LpWac4E-G	•	•	•	⦿	•	•						•	•
	NB1810-LpWac4Ep-G	•	•	•	⦿	•	•						•	•
	NB1810-NWac4Ep-G	•	•		⦿	•	•						•	•

[illegible]

Compliance Overview NetModule Products

Legend: • available ⦿ not necessary ⦿ in progress		Country Type Approvals						Vertical								Material	
		USA					RCM & R-NZ	Vehicles		Railway							
		Europe¹	UK	FCC	UL Safety	PTCRB	AT&T	Australia & New Zealand	E-Mark ECE R10	Fire Safety ECE R118	Onboard EN50155	Trackside EN50121-2	Fire Safety EN45545-2	Fire Safety NFPA130			
Vehicle Router	NG800-LjWWtGd2Br2CnHc	•	•	•					•	•					•	•	
	NG800-LWWtGd2Br2Cm	•	•	•					•	•					•	•	
	NG800-LWWtGd2Br2Cn	•	•	•					•	•					•	•	
	NG800-LWWtGd2Br2CnHc	•	•	•					•	•					•	•	
	NB2800-2L2Wac-G	•	•		•				•	•					•	•	
	NB2800-2L2WacDf-Gvi	•	•		•				•	•					•	•	
	NB2800-2Lp2Wac-G	•	•	•		•	•		•	•					•	•	
	NB2800-2Lp2WacDf-Gvi	•	•	•	•	•	•		•	•					•	•	
	NB2800-2LWac-G	•	•		•				•	•					•	•	
	NB2800-2LWacAp-GV	•	•		•				•	•					•	•	
	NB2800-2LWacDf-Gvi	•	•		•				•	•					•	•	
	NB2800-2LWacGd	•	•		•				•	•					•	•	
	NB2800-2LWacI-G	•	•		•				•	•					•	•	
	NB2800-2N-G	•	•		•				•	•					•	•	
	NB2800-2Wac	•	•	•	•	⦿	⦿		•	•					•	•	
	NB2800-4L-GV	•	•		•				•	•					•	•	
	NB2800-Lp2Wac-G	•	•	•	•				•	•					•	•	
	NB2800-LpWac-G	•	•	•	•				•	•					•	•	
	NB2800-LWac-G	•	•		•				•	•					•	•	
	NB2800-LWac2Cm-GFlx	•	•		•				•	•					•	•	
	NB2800-N2L-G	•	•		•				•	•					•	•	
	NB2800-N2Wac-G	•	•		•	•	•		•	•					•	•	
	NB2800-NLWac-GV	•	•		•				•	•					•	•	
	NB2800-NWac-G	•	•		•				•	•					•	•	
	NB2800-R	•	•	•	•	⦿	⦿		•	•					•	•	
	NB2810-2L2Wac-Gix	•	•		•				•	•					•	•	
	NB2810-2Lp2Wac-G	•	•	•	•				•	•					•	•	
	NB2810-2Lp2Wac-Gix	•	•	•	•				•	•					•	•	
	NB2810-2LWac-G	•	•		•				•	•					•	•	
	NB2810-2LWac2CmDf-GViFlx	•	•		•				•	•					•	•	
	NB2810-3Lp-G	•	•		•				•	•					•	•	
	NB2810-LpWacGd2Cm-ViFlx	•	•	•	•				•	•					•	•	
	NB2810-NLWac-G	•	•		•				•	•					•	•	
	NB2810-NWac-G	•	•		•				•	•					•	•	
	NB2810-NWac2CmDf-GViFlx	•	•		•				•	•					•	•	

Compliance Overview NetModule Products

Legend: • available ⦿ not necessary ⦿ in progress		Country Type Approvals							Vertical							Material	
		USA					RCM & R-NZ	Vehicles		Railway							
		Europe¹	UK	FCC	UL Safety	PTCRB	AT&T	Australia & New Zealand	E-Mark ECE R10	Fire Safety ECE R118	Onboard EN50155	Trackside EN50121-2	Fire Safety EN45545-2	Fire Safety NFPA130	RoHS	REACH	
Railway Router	NB3701-2Wac	•	•								•	•	•		•	•	
	NB3701-L-G	•	•								•	•	•		•	•	
	NB3701-LWac-G	•	•								•	•	•		•	•	
	NB3701-LWacPb-G	•	•								•	•	•		•	•	
	NB3800-2L2Wac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-2L2WacPb-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-2Lp-G	•	•	•	⦿						•	•	•	•	•	•	
	NB3800-2Lp2Wac-G	•	•	•	⦿	•	•				•	•	•	•	•	•	
	NB3800-2Lp2WacPb-G	•	•	•	⦿	•	•				•	•	•	•	•	•	
	NB3800-2LWac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-2LWacDf-Gvi	•	•		⦿				•	•	•	•	•	•	•	•	
	NB3800-2N-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-2NWac-G	•	•		⦿	•	•				•	•	•	•	•	•	
	NB3800-2NWacDf-Gvi	•	•		⦿	•	•				•	•	•	•	•	•	
	NB3800-3LpDf-Gvi	•	•		⦿						•	•	•	•	•	•	
	NB3800-3LWac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-L2WacCmI-GFlx	•	•		⦿						•	•	•	•	•	•	
	NB3800-LGrWac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-LpWac-G	•	•	•	⦿						•	•	•	•	•	•	
	NB3800-LWac-G	•	•		⦿				•	•	•	•	•	•	•	•	
	NB3800-LWacA-GV	•	•		⦿						•	•	•	•	•	•	
	NB3800-LWacAm-GV	•	•		⦿						•	•	•	•	•	•	
	NB3800-N-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-N2L-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-N2LWacDf-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-N2Wac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-NLWac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-NWac-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-NWac2D-G	•	•		⦿						•	•	•	•	•	•	
	NB3800-NWac2D2Cm-Gix	•	•		⦿						•	•	•	•	•	•	
	NB3800-NWac2D2CmDb-Gix	•	•		⦿						•	•	•	•	•	•	

Compliance Overview NetModule Products

Legend: • available 🕒 not necessary 🕒 in progress		Country Type Approvals						Vertical							
		USA					RCM & R-NZ	Vehicles		Railway				Material	
		Europe¹	UK	FCC	UL Safety	PTCRB	AT&T	Australia & New Zealand	E-Mark ECE R10	Fire Safety ECE R118	Onboard EN50155	Trackside EN50121-2	Fire Safety EN45545-2	Fire Safety NFPA130	RoHS
	AP3400-2Wax	•	•	•	🕒	🕒	🕒	•	•	•	•	•	•	•	•

Railway Access Point

Notes:

1) CE/RED compliance, countries: Austria, Belgium, Bulgaria, Croatia, Cyprus, Czech, Denmark, Estonia, Finland, France, Germany, Great Britain, Greece, Hungary
Ireland, Italy, Latvia, Lithuania, Luxembourg, Malta, Netherland, Poland, Portugal, Romania, Sweden, Slowakia, Slovenia, Spain, Iceland, Liechtenstein, Norway, Switzerland, Turkey

Update history

29. May 2024 - Initial version

13. Sept. 2024 - PTCRB & AT&T for NB1601 / NB800

24. Oct. 2024 - NB1601-Gr UL removed

02. March 2025 - AT&T Network Compatibility Approval for 5G product variants