



Product: [0905 204 301](#)



Life Cycle Status: Limited Availability/Passive

Cordset | 7/8" Female Straight → Open End, 5-pin, PUR (1.00 mm²) 18 AWG, 63 V / 9 A

Product Description

Single-Ended Cordset | 7/8" Female Straight, #Contacts 5 → Open End | Cable: Black PUR; 1.00 mm² (18 AWG) | 63 V / 9 A

Technical Drawing



Technical Specifications

Face View

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5
black 1	black 2	green / yellow	black 3	black 4

Technical Data

Product Family:	Power Connector
Side 1 Product Sub Family:	MINI 7/8"
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Side 1 Type of Contact/Gender:	Socket Contact / Female
Connector Design:	Molded 7/8" Female Straight
Number of Pins:	5 (4+PE)
Shielding Type:	Unshielded
Attachment Type:	Coupling Nut
Voltage Rating:	63 V
Operating Voltage:	50 V AC / 60 V DC
Current Rating:	9 A
Side 1 Contact Resistance:	$\leq 5 \text{ mOhm}$
Insulation Resistance:	$> 10^9 \text{ Ohm}$
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C to + 80 °C, notice derating

Protection Degree / IP Rating**:	IP65, IP67
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	Copper Alloy (CuZn)
Side 1 Contact Plating:	Copper-Silver-Gold-Alloy (Cu/Ag/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Grey
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Thermoplastic polyurethane (TPU)
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Polyamide (PA)

Additional Technical Data

Fastening Torque (Attachment):	7/8": 70 Ncm, hand-tight
--------------------------------	--------------------------

Cable Data

Cable Number:	204
Conductor Size:	1 mm²
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor Material:	Cu
Cable Jacket Material:	Polyurethane (PUR)
Cable Jacket Color:	Black
Cable Diameter D:	Ø 8.0 0.315"
Wire Insulation Material:	Polypropylene (PP)
Insulated Wire Diameter:	Ø 2.35 mm 0.092"
Overall Shield (Cable):	Unshielded
Ambient Temperature (Fixed Installation):	- 40 °C to + 80 °C
Ambient Temperature (Flex Installation):	- 25° C to + 80° C
Ambient Temperature (Drag Chain Inst):	- 25° C to + 60 ° C
UL Cable Type:	AWM Style 20549
Flammability Class (Cable Jacket):	DIN EN 60332-2-2 VDE 0482-332-2-2 IEC 60332-2-2 CSA FT-2

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Halogenfree:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1
Oil Resistance:	Yes

Notes

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
Note:	1. Do not connect or disconnect under load.

Variants

Item #	Item Description	Cable Length
101739	0905 204 301/0,3 M	0.3 m
13528	0905 204 301/1 M	1 m
108770	0905 204 301/1,5 M	1.5 m
104942	0905 204 301/2 M	2 m
13527	0905 204 301/3 M	3 m
13504	0905 204 301/5 M	5 m
394	0905 204 301/7 M	7 m
55600	0905 204 301/10 M	10 m
81914	0905 204 301/15 M	15 m
76615	0905 204 301/20 M	20 m

78045	0905 204 301/25 M	25 m
395	0905 204 301/30 M	30 m
396	0905 204 301/40 M	40 m
392	0905 204 301/45 M	45 m

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.