



Product: [0905 204 302](#) 


Life Cycle Status: Limited Availability/Passive

Cordset | 7/8" Female Straight → 7/8" Male Straight, 5-pin, PUR (1.00 mm²) 18 AWG, 63 V / 9 A

Product Description

Doubled-Ended Cordset | 7/8" Female Straight, #Contacts 5 → 7/8" Male Straight, #Contacts 5 | Cable: Black PUR; 1.00 mm² (18 AWG) | 63 V / 9 A

Technical Drawing



Technical Specifications

Face View Side 1

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5
black 1	black 2	green / yellow	black 3	black 4

Face View Side 2

Pin 1	Pin 2	Pin 3	Pin 4	Pin 5
-------	-------	-------	-------	-------

Product Description

Product Family:	Power Connector
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding Type:	Unshielded
Voltage Rating:	63 V
Operating Voltage:	50 V AC / 60 V DC
Current Rating:	9 A

Technical Data Side 1

Side 1 Product Sub Family:	MINI 7/8"
Side 1 Type of Contact/Gender:	Pin Contact / Male
Connector Design:	Molded 7/8" Male Straight
Attachment Type:	Coupling Screw
Number of Pins:	5 (4+PE)
Side 1 Contact Resistance:	≤ 5 mOhm
Insulation Resistance:	> 10^9 Ohm
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C to + 80 °C, notice derating
Protection Degree / IP Rating**:	IP65, IP67
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	Copper Alloy (CuZn)
Side 1 Contact Plating:	Copper-Silver-Gold-Alloy (Cu/Ag/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Grey
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	Thermoplastic polyurethane (TPU)
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Polyamide (PA)
Fastening Torque (Attachment):	7/8": 70 Ncm, hand-tight
Note:	1. Do not connect or disconnect under load.

Cable Data

Cable Number:	204
Conductor Size:	1 mm²
Minimal Bending Radius (Fixed Inst):	> 5 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor Material:	Cu
Cable Jacket Material:	Polyurethane (PUR)
Cable Jacket Color:	Black
Cable Diameter D:	Ø 8.0 0.315"
Wire Insulation Material:	Polypropylene (PP)
Insulated Wire Diameter:	Ø 2.35 mm 0.092"
Overall Shield (Cable):	Unshielded
Ambient Temperature (Fixed Installation):	- 25° C to + 60 ° C
Ambient Temperature (Flex Installation):	- 25° C to + 80° C
Ambient Temperature (Drag Chain Inst):	- 25° C to + 60 ° C
UL Cable Type:	AWM Style 20549
Flammability Class (Cable Jacket):	DIN EN 60332-2-2 VDE 0482-332-2-2 IEC 60332-2-2 CSA FT-2

Technical Data Side 2

Side 2 Product Sub Family:	MINI 7/8"
Side 2 Type of Contact/Gender:	Socket Contact / Female
Connector Design, Side 2:	Molded 7/8" Female Straight

Attachment Type, Side 2:	Coupling Nut
Number of Pins, Side 2:	5 (4+PE)
Contact Resistance, Side 2:	≤ 5 mOhm
Insulation Resistance, Side 2:	> 10^9 Ohm
Mating Cycles, Side 2:	≤ 100
Ambient Temperature (Operation), Side 2*:	- 40 °C to + 80 °C, notice derating
Protection Degree / IP Rating, Side 2**:	IP65, IP67
Contact Base Material, Side 2:	Copper Alloy (CuZn)
Contact Bearer Material, Side 2:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color, Side 2:	Grey
Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Molded Body Material, Side 2:	Thermoplastic Elastomer (TPE)
Molded Body Color, Side 2:	Black
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Polyamide (PA)
Fastening Torque (Attachment), Side 2:	7/8": 70 Ncm, hand-tight
Note, Side 2:	1. Do not connect or disconnect under load.

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Halogenfree:	DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1
Oil Resistance:	Yes

Notes

Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
Note Derating:	* Notice derating

Variants

Item #	Item Description	Cable Length
28411	0905 204 302/0,3 M	0.3 m
84214	0905 204 302/0,6 M	0.6 m
78774	0905 204 302/1 M	1 m
934636323	0905 204 302/1,5 M	1.5 m
78806	0905 204 302/2 M	2 m
94931	0905 204 302/3 M	3 m
934637816	0905 204 302/4 M	4 m
81778	0905 204 302/5 M	5 m
934637817	0905 204 302/6 M	6 m
96248	0905 204 302/8 M	8 m
387	0905 204 302/9 M	9 m
78890	0905 204 302/10 M	10 m
89018	0905 204 302/12 M	12 m
78769	0905 204 302/15 M	15 m
88733	0905 204 302/20 M	20 m
78771	0905 204 302/25 M	25 m
78773	0905 204 302/30 M	30 m
107449	0905 204 302/45 M	45 m

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.