

**Product:** [0935 613 303](#) 




CANopen / DeviceNet, Cordset, single ended: 7/8", Female, Straight, 5 pole, with cable type, Grey, PVC, DeviceNet THICK

**Product Description**


CANopen / DeviceNet, Cordset, single ended: 7/8", Female, Straight, 5 pole, with cable type, Grey, PVC, DeviceNet THICK

**Technical Drawing**

Faceview  
MINI 7/8"  
Female



- 1 = Cu
- 2 = RD
- 3 = BK
- 4 = WH
- 5 = BU



**Technical Specifications**

**Technical Data**

Product Family:	Data Connectors
Product Sub Family:	7/8"
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Female
Connector Design:	Straight
Number of Pins:	5
Coding:	A
Shielding:	Shielded
Attachment Type:	Coupling Nut with internal threads
Rated Voltage:	300 V
Rated Current*:	8 A

Data Transmission:	CANopen / DeviceNet
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating**:	IP65, IP67

## Materials

Contact Base Material:	CuZn
Contact Plating:	gold over silver plated
Contact Bearer Material:	TPU
Contact Bearer Color:	Yellow
Molded Body Material:	TPU
Molded Body Color:	Grey
Housing Color:	yellow
Attachment Material:	Al, anodized black

## Cable Data

Cable Number:	613
Number of Wires:	2 Pair + Drain
Minimal Bending Radius (Fixed Inst):	> 7 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 1 M
Cable Jacket Material:	PVC
Cable Jacket Color:	Grey
Cable Diameter D:	Ø 12.1 mm
Wire Insulation Material:	PVC-Power, Data-PE
Insulated Wire Diameter:	Power Ø2.77 mm, Data Ø3.81 mm
Overall Shield (Cable):	Braid, TC, 65% Coverage
Ambient Temperature (Fixed Installation):	- 20 to + 60°C (60°C UL)
UL Cable Type:	CMG, PLTC-ER or UL AWM 20201, CSA AWM I/II A/B
Flammability Class (Cable Jacket):	FT4, IEC 60332-1-2
Cable Characteristics:	Mechanical Resistances, Abrasion, Impact, Weathering; Chemical Resistances to Oils, Acids, Alkalis

## Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

## Resistances

Oil Resistance:	Yes
-----------------	-----

## Notes

Note Derating:	Notice derating
Protection Degree / IP Rating Note:	Protection Degree and IP Rating per test standard IEC 60529 using a Lumberg Automation mating product

## Variants

Item #	Item Description	Cable Length
900001561	0935 613 303/0.3M	0.3 m
910001561	0935 613 303/0.3M-Y	0.3 m
900004485	0935 613 303/0.6M	0.6 m
900002965	0935 613 303/1M	1 m
910002965	0935 613 303/1M-Y	1 m
900001748	0935 613 303/2M	2 m
71282	0935 613 303/2 M	2 m
910001748	0935 613 303/2M-Y	2 m
900001719	0935 613 303/3M	3 m
910001719	0935 613 303/3M-Y	3 m
900001749	0935 613 303/4M	4 m
910001749	0935 613 303/4M-Y	4 m
900002964	0935 613 303/5M	5 m
910002964	0935 613 303/5M-Y	5 m
900004437	0935 613 303/6M	6 m
900001562	0935 613 303/9M	9 m

910001562	0935 613 303/9M-Y	9 m
900001957	0935 613 303/10M	10 m
9991	0935 613 303/10 M	10 m
910001957	0935 613 303/10M-Y	10 m
900002314	0935 613 303/15M	15 m
910002314	0935 613 303/15M-Y	15 m
900001822	0935 613 303/20M	20 m
910001822	0935 613 303/20M-Y	20 m
900001564	0935 613 303/25M	25 m
910001564	0935 613 303/25M-Y	25 m
900001559	0935 613 303/30M	30 m
910001559	0935 613 303/30M-Y	30 m
900001560	0935 613 303/35M	35 m
910001560	0935 613 303/35M-Y	35 m
900002315	0935 613 303/40M	40 m
910002315	0935 613 303/40M-Y	40 m
900004042	0935 613 303/50M	50 m
910004042	0935 613 303/50M-Y	50 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.