

Product: [0935 614 306](#) 




CANopen / DeviceNet, Cordset, single ended: 7/8", Female, Angled, 5 pole, with cable type, Grey, PVC, DeviceNet THIN

Product Description


CANopen / DeviceNet, Cordset, single ended: 7/8", Female, Angled, 5 pole, with cable type, Grey, PVC, DeviceNet THIN

Technical Drawing

Faceview
MINI 7/8"
Female



1 = Cu
2 = RD
3 = BK
4 = WH
5 = BU



Technical Specifications

Technical Data

Product Family:	Data Connectors
Side 1 Product Sub Family:	7/8"
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Side 1 Type of Contact/Gender:	Female
Connector Design:	Angled
Number of Pins:	5
Coding, Side 1:	A
Shielding Type:	Shielded
Attachment Type:	Coupling Nut with internal threads
Voltage Rating:	250 V
Current Rating:	4 A

Data Transmission Type:	CANopen / DeviceNet
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating**:	IP65, IP67

Materials

Contact Base Material:	CuZn
Side 1 Contact Plating:	gold over silver plated
Contact Bearer Material:	TPU
Contact Bearer Color:	Yellow
Molded Body Material:	TPU
Molded Body Color:	Grey
Attachment Material:	Al, anodized black

Cable Data

Cable Number:	614
Conductor Size:	5x 0.34 mm²
Number of Wires:	2 Pair + Drain
Minimal Bending Radius (Fixed Inst):	> 7 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 1 M
Cable Jacket Material:	PVC
Cable Jacket Color:	Grey
Cable Diameter D:	Ø 7.11 mm
Wire Insulation Material:	PVC-Power, Data-PE
Insulated Wire Diameter:	Power Ø1.80 mm, Data Ø2.00 mm
Overall Shield (Cable):	Braid, TC, 65% Coverage
Ambient Temperature (Fixed Installation):	- 20 to + 60°C (60°C UL)
UL Cable Type:	UL AWM 20201, CSA AWM I/II A/B
Flammability Class (Cable Jacket):	FT4, IEC 60332-1-2
Cable Characteristics:	Mechanical Resistances, Abrasion, Impact, Weathering; Chemical Resistances to Oils, Acids, Alkalis

Approvals

UL:	UL
-----	----

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Oil Resistance:	Yes
-----------------	-----

Notes

Note Derating:	Notice derating
Protection Degree / IP Rating Note:	Protection Degree and IP Rating per test standard IEC 60529 using a Lumberg Automation mating product

Variants

Item #	Item Description	Cable Length
900004317	0935 614 306/0.3M	0.3 m
900004318	0935 614 306/1M	1 m
900004319	0935 614 306/2M	2 m
900004320	0935 614 306/3M	3 m
900004321	0935 614 306/5M	5 m
900004322	0935 614 306/10M	10 m

at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.