


**Product:** [0935 709 104](#) 




CANopen / DeviceNet, Cordset, single ended: M12 Standard, Male, Straight, 5 pole, with cable type, Black, TPE, DeviceNet MID

### Product Description


CANopen / DeviceNet, Cordset, single ended: M12 Standard, Male, Straight, 5 pole, with cable type, Black, TPE, DeviceNet MID

### Technical Drawing

## Faceview M12 Male



- 1 = Cu
- 2 = RD
- 3 = BK
- 4 = WH
- 5 = BU



### Technical Specifications

#### Technical Data

Product Family:	Data Connectors
Side 1 Product Sub Family:	M12 Standard
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Side 1 Type of Contact/Gender:	Male
Connector Design:	Straight
Number of Pins:	5
Coding, Side 1:	A
Shielding Type:	Shielded
Attachment Type:	Coupling Screw with external threads
Voltage Rating:	250 V
Current Rating:	4 A

Data Transmission Type:	CANopen / DeviceNet
Ambient Temperature (Operation)*:	- 40 °C - + 90 °C
Protection Degree / IP Rating**:	IP65, IP67

## Materials

Contact Base Material:	CuSn
Side 1 Contact Plating:	Cu/Au
Contact Bearer Material:	TPU
Contact Bearer Color:	Yellow
Molded Body Material:	TPU
Molded Body Color:	Grey
Attachment Material:	CuZn, Nickel-plated

## Cable Data

Cable Number:	709
Number of Wires:	2 Pair + Drain
Minimal Bending Radius (Fixed Inst):	> 7 x D
Minimal Bending Radius (Flexible Inst):	> 10 x D
Cycles (Bending):	> 10 M
Cable Jacket Material:	TPE
Cable Jacket Color:	Black
Cable Diameter D:	Ø 9.65 mm
Wire Insulation Material:	PVC-Power, Data-PP
Insulated Wire Diameter:	Power Ø2.48mm, Data Ø2.75mm
Overall Shield (Cable):	Overall Braid, TC, 65% Coverage, Pairs Alum+Poly 100% coverage
Ambient Temperature (Fixed Installation):	- 20 to + 70°C
UL Cable Type:	UL AWM 20626, CSA AWM I/II A/B
Flammability Class (Cable Jacket):	FT1
Cable Characteristics:	Mechanical Resistances, Abrasion, Impact, Weathering; Chemical Resistances to Oils, Acids, Alkalis; High Flex, C-Track Rated

## Approvals

UL:	UL
-----	----

## Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

## Resistances

Oil Resistance:	Yes
-----------------	-----

## Notes

Note Derating:	Notice derating
Protection Degree / IP Rating Note:	Protection Degree and IP Rating per test standard IEC 60529 using a Lumberg Automation mating product

## Variants

Item #	Item Description	Cable Length
600004344	0935 709 104/1M	1 m
600004345	0935 709 104/3M	3 m
600004346	0935 709 104/5M	5 m
600004347	0935 709 104/10M	10 m

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.