




Product: [0985 YM57530 103](#)

Fast Ethernet Cat5e, double-ended cord set, M12 male, straight, 4-pin, D-coding to a RJ45 male, straight, 8-pin, 24 AWG TPE cable, stranded/shielded, 2 twisted bonded pairs with teal jacket


Product Description

Fast Ethernet Cat5e, double-ended cord set, M12 male, straight, 4-pin, D-coding to a RJ45 male, straight, 8-pin, 24 AWG TPE cable, stranded/shielded, 2 twisted bonded pairs with teal jacket

Technical Drawing




Technical Data Side 1
M12 Male



Color Code

1 = WH/OR
2 = WH/GN
3 = OR
4 = GN
Shield = Coupling Nut

Technical Data Side 2
RJ45 Male



Color Code

1 = WH/OR
3 = WH/GN
2 = OR
6 = GN
Shield = RJ45 Sleeve

Technical Specifications

Product Description

Product Family:	Data Connectors
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding:	Shielded
Rated Voltage:	42 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	30 V AC/ 42 V DC
Rated Current*:	1.5 A
Data Transmission:	Fast Ethernet Cat5e
Data Transmission Rate:	100 Mbit/s

Technical Data Side 1

Product Sub Family:	M12 Standard
Type of Contact / Gender:	Male
Connector Design:	Straight
Attachment Type:	Knurled Screw
Number of Pins:	4

Coding:	D
Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 25 °C - + 75 °C
Protection Degree / IP Rating**:	IP65, IP67
Design Standard:	IEC 61076-2-101
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	CuSn
Contact Plating:	Cu/Au
Contact Bearer Material:	PBT
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	TPU
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	CuZn
Attachment Plating:	Nickel-plated
Shielding Material:	CuZn, tin-plated
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight

Cable Data

Cable Type:	103
Cable Number:	YM57530
Conductor Size:	24 AWG
Number of Wires:	2 Pair (bonded twisted pairs)
Minimal Bending Radius (Fixed Inst):	5 x D
Minimal Bending Radius (Flexible Inst):	10 x D
Cycles (Bending):	3
Cycles (Torsion):	> 5 M @ ± 360 °/1 m
Cable Jacket Material:	TPE
Cable Jacket Color:	Teal
Cable Diameter D:	ø 7.62 mm
Wire Insulation Material:	Polyolefin
Insulated Wire Diameter:	ø 1.02 ± 0.05 mm
Overall Shield (Cable):	TC Braid 65%
Foil shield:	Al Foil 100%
Ambient Temperature (Fixed Installation):	- 40 °C - + 75 °C
Ambient Temperature (Flex Installation):	- 25 °C - + 75 °C
Ambient Temperature (Drag Chain Inst):	- 25 °C - + 60 °C
UL Cable Type:	AWM 20626, 80C 600 V
Cable Characteristics:	NEMA WC-63.1 Category 5, ICEA 661, Category 5e Patch, TIA/EI-568-B.2, Category 5e, Indoor/Outdoor Yes, Oil Res
Core Colors:	Bonded Twisted pairs: wh/or wh/gn

Technical Data Side 2

Product Sub Family, Side 2:	RJ45
Type of Contact / Gender, Side 2:	Male
Connector Design, Side 2:	Straight
Attachment Type, Side 2:	Plug
Number of Pins, Side 2:	8 (4 terminated)
Coding, Side 2:	RJ45
Mating Cycles, Side 2:	≤ 750
Ambient Temperature (Operation), Side 2*:	- 40 °C - + 70 °C
Protection Degree / IP Rating, Side 2**:	IP20
Contact Base Material, Side 2:	P / CuSN
Contact Plating, Side 2:	Au
Contact Bearer Material, Side 2:	Polycarbonate
Contact Bearer Color, Side 2:	Clear

Molded Body Material, Side 2:	Elastomer Polyolefin
Molded Body Color, Side 2:	Black

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Oil Resistance:	Yes
-----------------	-----

Notes

Note Derating:	Notice derating
----------------	-----------------

History

Update and Revision:	Revision Number: 0.37 Revision Date: 08-25-2022
----------------------	---

Variants

Item #	Item Description	Cable Length
900004145	0985 YM57530 103/0.15M	0.15 m
900004146	0985 YM57530 103/0.25M	0.25 m
900004847	0985 YM57530 103/0.3M	0.3 m
900016223	0985 YM57530 103/0.5M	0.5 m
900004848	0985 YM57530 103/0.6M	0.6 m
900004147	0985 YM57530 103/1M	1 m
900004148	0985 YM57530 103/2M	2 m
900004149	0985 YM57530 103/3M	3 m
900004436	0985 YM57530 103/4M	4 m
900004150	0985 YM57530 103/5M	5 m
900005130	0985 YM57530 103/6M	6 m
900004420	0985 YM57530 103/7M	7 m
900004151	0985 YM57530 103/10M	10 m
900005273	0985 YM57530 103/12M	12 m
900004152	0985 YM57530 103/15M	15 m
900004153	0985 YM57530 103/20M	20 m
900004416	0985 YM57530 103/25M	25 m
900004154	0985 YM57530 103/30M	30 m
900004417	0985 YM57530 103/35M	35 m
900004418	0985 YM57530 103/40M	40 m
900016315	0985 YM57530 103/45M	45 m
900004419	0985 YM57530 103/50M	50 m
900016316	0985 YM57530 103/60M	60 m
900004421	0985 YM57530 103/80M	80 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.