

Product: [0985 806 101](#)





Fast Ethernet Cat 5e, high-flex, double-ended cord set, M12 male to M12 male, teal TPE jacket, 4-pin, 24 AWG, stranded/unshielded cross-over cable with 2 twisted bonded pairs.

Product Description

Fast Ethernet Cat 5e, high-flex, double-ended cord set, M12 male to M12 male, teal TPE jacket, 4-pin, 24 AWG, stranded/unshielded cross-over cable with 2 twisted bonded pairs.

Technical Drawing



Technical Specifications

Product Description

Product Family:	Data Connectors
Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Shielding:	Unshielded
Rated Voltage:	60 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	250V
Rated Current*:	4 A
Data Transmission:	Fast Ethernet Cat5e
Data Transmission Rate:	100 Mbit/s

Technical Data Side 1

Product Sub Family:	M12 Standard
Type of Contact / Gender:	Pin Contact / Male
Connector Design:	Straight
Attachment Type:	Coupling Screw
Number of Pins:	4
Coding:	D
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	250V
Mating Cycles:	≤ 100
Cable Gland:	PG 11
Strain-Relief:	Cable clamp
Ambient Temperature (Operation)*:	- 40 °C - + 75 °C
Protection Degree / IP Rating**:	IP68

Design Standard:	IEC 61076-2-101
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance:	EN 60664-1 (2008/01); VDE 0110-1
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material:	Copper and Tin (CuSn)
Contact Plating:	Copper over Gold (Cu/Au)
Contact Bearer Material:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	TPU
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 HB
Housing Color:	black
Attachment Material:	Brass (Cu/Zn)
Attachment Plating:	Nickel (Ni)
Gasket Material:	SBR/NBR, cable gland
Fastening Torque (Cable Gland):	PG11: (250-375) Ncm
Fastening torque (mounting screw):	BZ 2,9x14: (40-50) Ncm
Fastening Torque (Attachment):	M 12x1: (50-60) Ncm, hand-tight
Accessories to Order Separately:	732-045-001, STASI 3, securing clip

Cable Data

Cable Number:	806
Conductor Size:	24 AWG
Number of Wires:	4 (2 twisted pairs)
Minimal Bending Radius (Fixed Inst):	.250"
Cycles (Bending):	> 2 M
Conductor material:	Cu
Cable Jacket Material:	Thermoplastic Elastomer (TPE)
Cable Jacket Color:	Teal
Cable Diameter D:	.275"
Wire Insulation Material:	PO
Insulated Wire Diameter:	.037"
Ambient Temperature (Fixed Installation):	-50°C + 75°C
UL Cable Type:	Cat 5e
Flammability Class (Cable Jacket):	UL: CMR / CSA: CMG
Core Colors:	White / Orange, White / Green, Orange, Green

Technical Data Side 2

Product Sub Family, Side 2:	M12 Standard
Type of Contact / Gender, Side 2:	Pin Contact / Male
Connector Design, Side 2:	Straight
Attachment Type, Side 2:	Coupling Screw
Number of Pins, Side 2:	4
Coding, Side 2:	D
Contact Resistance, Side 2:	≤ 10 mOhm
Insulation Resistance, Side 2:	> 10 ⁹ Ohm
Mating Cycles, Side 2:	≤ 100
Ambient Temperature (Operation), Side 2*:	- 40 °C - + 75 °C
Protection Degree / IP Rating, Side 2**:	IP68
Design Standard, Side 2:	IEC 61076-2-101
Pollution Degree, Side 2:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category, Side 2:	III acc. to DIN EN 60664-1 (VDE 0110-1)
Contact Base Material, Side 2:	Phosphorus / Copper and Tin (CuSn)
Contact Plating, Side 2:	Copper over Gold (Cu/Au)
Contact Bearer Material, Side 2:	Thermoplastic Polyurethane (TPU)
Contact Bearer Color, Side 2:	Black

Flammability Class (Contact Bearer), Side 2:	UL 94 HB
Molded Body Material, Side 2:	Thermoplastic Polyurethane (TPU)
Molded Body Color, Side 2:	Black
Flammability Class (Molded Body), Side 2:	UL 94 HB
Attachment Material, Side 2:	Brass (Cu/Zn)
Attachment Plating, Side 2:	Nickel (Ni)
Fastening Torque (Attachment), Side 2:	M 12x1: (50-60) Ncm, hand-tight

Safety & Environmental Compliance

RoHS Compliant:	yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	IP Rating tested according to IEC standard using combination of a Hirschmann or Lumberg Automation connector mounted and locked
Note Derating:	Notice derating

History

Update and Revision:	Revision Number: 0.40 Revision Date: 07-07-2025
----------------------	---

Variants

Item #	Item Description	Cable Length
900004841	0985 806 101/0.5M	0.5 m
900016125	0985 806 101/1M	1 m
900004068	0985 806 101/2M	2 m
900004246	0985 806 101/5M	5 m
900005277	0985 806 101/10M	10 m
900016017	0985 806 101/15M	15 m

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.