

Product: 1000AE

Type JX Thermocouple, 1 Pr #16 Sol, PVC-Nylon White, Red, OS, Black PVC Jkt, 300V PLTC-ER ITC CMG

Product Description

Type JX Thermocouple, 1 Pair 16AWG (Solid) OFHC+Constantan, PVC-Nylon White, Red Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC CMG AWM 2464 SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	Exposed Runs, Hazardous Locations,PLC,4-20ma

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	16	Solid	Iron & Constantan

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter
Pair(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.016 in (0.41 mm)	0.085 in (2.2 mm)

Outer Jacket

Nom. Thickness	Nom. Diameter	Ripcord
0.040 in (1.0 mm)	0.304 in (7.72 mm)	Yes

Electrical Characteristics

Voltage

UL Voltage Rating
300 V RMS (PLTC)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

Bulk Cable Weight:	53 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL1685 FT4 Loading
NEC / UL Compliance:	CMG, ITC, PLTC
CEC / C(UL) Compliance:	CMG
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alternate color coding available upon request.

History

Update and Revision:	Revision Number: 0.58 Revision Date: 10-30-2026

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.