



Product: [0985 856 103](#) 

Industrial Ethernet double-ended cord set, high-flex, male, M12 to RJ45 straight, 4 Bonded-Twisted pairs, 24 AWG, TPE cable, stranded/shielded with teal jacket and orange inserts.

Product Description

Industrial Ethernet double-ended cord set, high-flex, male, M12 to RJ45 straight, 4 Bonded-Twisted pairs, 24 AWG, TPE cable, stranded/shielded with teal jacket and orange inserts.

Technical Specifications

Product Description

Brand:	Lumberg Automation
Connector Type:	Cordset, double ended
Voltage Rating:	600V according to UL 20626
Data Transmission Rate:	100 Mbit/s

Technical Data Side 1

Connector Design:	Straight
Attachment Type:	Coupling Screw
Coding, Side 1:	A
Side 1 Contact Resistance:	≤ 10 mOhm
Ambient Temperature (Operation)*:	-40° C(-40°F) to +75° C(+167°F)
Protection Degree / IP Rating**:	IP67
Side 1 Design Standard:	IEC 61076-2-101
Side 1 Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Clearance / Creepage Distance:	EN 60664-1 (2008/01); VDE 0110-1
Contact Base Material:	Copper and Tin (CuSn)
Side 1 Contact Plating:	Copper over Gold (Cu/Au)
Contact Bearer Material:	PUR
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Molded Body Material:	PUR, black
Flammability Class (Molded Body):	UL 94 HB
Attachment Material:	Brass (Cu/Zn)
Attachment Plating:	Nickel (Ni)

Cable Data

Cable Number:	856
Conductor Size:	24 AWG
Cycles (Bending):	> 5 M
Cable Jacket Material:	Thermoplastic Elastomer (TPE)
Cable Jacket Color:	Teal
Cable Diameter D:	7.6 mm nominal
Foil shield:	Aluminum/polyester/aluminum foil, 100% coverage
Cable Characteristics:	600 V AWM 20626, C(UL) US CMR, CSA FT4
Core Colors:	white/orange, orange, white/blue, blue, white/green, green, white/brown,brown

Technical Data Side 2

Attachment Type, Side 2:	RJ45
Ambient Temperature (Operation), Side 2*:	-40° C(-40°F) to +75° C(+167°F)
Contact Base Material, Side 2:	P / CuSN
Contact Plating, Side 2:	Au
Contact Bearer Material, Side 2:	Plastic
Molded Body Material, Side 2:	PUR, black
Attachment Material, Side 2:	Plastic
Attachment Plating, Side 2:	Au

History

Update and Revision:	Revision Number: 0.10 Revision Date: 03-02-2026
----------------------	---

Variants

Item #	Item Description
900016059	0985 856 103/1.5M
900016060	0985 856 103/2M
900016061	0985 856 103/2.5M
900016062	0985 856 103/3M
900016064	0985 856 103/4M
900016065	0985 856 103/5M
900016066	0985 856 103/6M
900016067	0985 856 103/8M
900016056	0985 856 103/0.3M
900016057	0985 856 103/0.6M
900016058	0985 856 103/1M
900016068	0985 856 103/10M
900016069	0985 856 103/12M
900016070	0985 856 103/15M
900016071	0985 856 103/20M
900016072	0985 856 103/25M
900016073	0985 856 103/40M
900016074	0985 856 103/50M
900016430	0985 856 103/0.5M

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.