



REPRESENTATIVE IMAGE

**Product:** [1018A](#)

Type KX Thermocouple, 1 Pr #16 Sol, PVC Ins Yel, Red, OS, Yellow PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

## Product Description

Type KX Thermocouple, 1 Pair 16AWG (Solid) Chromel+Alumel, PVC Insulation Yel, Red Color Code, Overall Beldfoil® Shield, Yellow PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES

## Technical Specifications

### Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), Thermocouple, distributed control system (DCS), programmable logic controller (PLC)
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	16 AWG	Solid	Chromel & Alumel

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	0.093 in (2.4 mm)	Yellow & Red

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.264 in (6.71 mm)	Yes

Overall Cable Diameter (Nominal): 0.264 in (6.71 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield
Pair(s)	25 pF/ft (82 pF/m)	51 pF/ft (170 pF/m)

Table Notes: Conductor DCR (Nom): 165 Ohm/1000ft (Chromel), 66 Ohm/1000ft (Alumel)

#### Voltage

UL Voltage Rating
300 V (PLTC-ER, CMG, UL AWM 2464), 150 V (ITC-ER)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

#### Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension:	83 lbs
Bulk Cable Weight:	38 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 (FT4 Loading), FT4, 1202
NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, PLTC-ER, ITC-ER
AWM Compliance:	2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA MC 96.1-1982 Type KX

## Product Notes

Notes:	Chromel and Alumel are Hoskins Manufacturing Company trademarks.
--------	--

## History

Update and Revision:	Revision Number: 0.375 Revision Date: 10-27-2021
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC
1018A 0041000	Yellow	Reel	1,000 ft	612825103837
1018A 0045000	Yellow	Reel	5,000 ft	612825103851
1018A 00410000	Yellow	Reel	10,000 ft	612825103844

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.