



Part Number: 1032A

Inst, 1 Pr #18 Str BC, PVC Ins E1, OS, Blk PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

Product Description

UL Instrumentation, 1 Pair 18AWG (7x26) Bare Copper, PVC Insulation E1 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
18	7x26	BC - Bare Copper	1

Conductor Count:	2
Total Number of Pairs:	1
Total Number of Triads:	N/A

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.016 in

Color Chart

Number	Color
1	Black and White

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.237 in	0.037 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	5.07 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
51 pF/ft	95 pF/ft

Inductance

Nominal Inductance
0.19 µH/ft

Current

Max. Recommended Current [A]
8 Amps per conductor @ 25°C

Voltage

UL Description	UL Voltage Rating
PLTC, CMG	300 V RMS
ITC	150 V RMS

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	32.5 lbs/1000ft
Max Recommended Pulling Tension:	26 lbs
Min Bend Radius/Minor Axis:	2.3 in

Standards

NEC/(UL) Specification:	CMG, ITC, PLTC
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2464 (300 V 80°C)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	No
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
1032A 0101000	Black	612825104988	1,000 ft	C
1032A 01010000	Black	612825104995	10,000 ft	C Z
1032A 0061000	Blue, Light	612825104957	1,000 ft	C
1032A 00610000	Blue, Light	612825104964	10,000 ft	C
1032A 0065000	Blue, Light	612825104971	5,000 ft	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Alternate color coding available upon request.
--------	--

History

Update and Revision:

Revision Number: 0.305 Revision Date: 09-10-2019

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.