



Product: [1063S](#)

Inst, 2 Pr #18 Str BC, XLPE Ins E1,OS, Bk LSZH PE Jkt, 600V TC 90C
Dry/Wet SUN RES DIR BUR

Product Description

UL Instrumentation, 2 Pair 18AWG (7x26) Bare Copper, XLPE Insulation E1 Color Code, Overall Beldfoil® Shield, Black LSZH PE Outer Jacket, 600V TC 90C Dry/Wet SUN RES DIR BUR

Technical Specifications

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	18 AWG	7x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	XLP, XLPO, XLPE (Thermoset)	0.031 in (0.79 mm)	0.109 in (2.77 mm)	ICEA S-73-732 Table E1; Black & White and Numbered

Inner Shield

Material
No Shield

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.047 in (1.2 mm)	0.490 in	Yes

Overall Cable Diameter (Nominal):	0.490 in
-----------------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
7.0 Ohm/1000ft	11 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
600 V (TC-ER)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-30°C To +90 °C Dry/Wet

Bend Radius

Stationary Min.	Installation Min.

5.88 in (149 mm)	5.88 in
------------------	---------

Max. Pull Tension:	112 lbs (50.8 kg)
Bulk Cable Weight:	85 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 760, TC-ER
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alternate color coding available upon request.
--------	--

History

Update and Revision:	Revision Number: 0.47 Revision Date: 04-08-2022
----------------------	---

Part Numbers

Variants

Item #	Putup Type
1063S 0105000	Reel

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.