



Part Number: 1081A

300V, (36 pr) 20 AWG (7x28), (1) 22 AWG (7x30) BC, PVC/PVC, IS/OS, PLTC-ER, CMG

Product Description

Thirty-six 20 AWG pairs stranded (7x28) bare copper conductors plus one 22 AWG stranded (7x30) bare copper conductor, twisted pairs, PVC insulation, individual plus an overall Beldfoil® shield (100% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
20	7x28	BC - Bare Copper		36
22	7x30	BC - Bare Copper	1	

Conductor Count:	73
Total Number of Pairs:	36
Total Number of Triads:	N/A
Conductor Size:	20 AWG

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.0175 in
PVC - Polyvinyl Chloride	0.019 in

Color Chart

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2
3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10
11	Black & White and Numbered 11
12	Black & White and Numbered 12
13	Black & White and Numbered 13
14	Black & White and Numbered 14
15	Black & White and Numbered 15
16	Black & White and Numbered 16
17	Black & White and Numbered 17
18	Black & White and Numbered 18
19	Black & White and Numbered 19
20	Black & White and Numbered 20
21	Black & White and Numbered 21
22	Black & White and Numbered 22
23	Black & White and Numbered 23
24	Black & White and Numbered 24

25	Black & White and Numbered 25
26	Black & White and Numbered 26
27	Black & White and Numbered 27
28	Black & White and Numbered 28
29	Black & White and Numbered 29
30	Black & White and Numbered 30
31	Black & White and Numbered 31
32	Black & White and Numbered 32
33	Black & White and Numbered 33
34	Black & White and Numbered 34
35	Black & White and Numbered 35
36	Black & White and Numbered 36
37	Orange

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm
					TC - Tinned Copper	

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	1.091 in	0.074 in	Yes

Construction and Dimensions

Cabling

Lay Direction

Left Hand

Print Legend:

LEGEND: BELDEN 1081A E34972 36PR20 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG ----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	6.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
30 pF/ft	55 pF/ft

Shielding: Individually Foiled + Overall Foil

Inductance

Nominal Inductance

0.19 µH/ft

Current

Max. Recommended Current [A]

3 Amps per conductor @ 25°C

Voltage

UL Voltage Rating

300 V RMS

150 V RMS (ITC)

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	633 lbs/1000ft
Max Recommended Pulling Tension:	1359 lbs
Min Bend Radius/Minor Axis:	10.5 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 UL Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
1081A 0102000	Black	C Z

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.