



Part Number: 1085A

Inst, 12 Tri #20+22 Str BC, PVC Ins E1, IS/OS, Blk PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

Product Description

UL Instrumentation, 12 Triad 20+22AWG (7x28) Bare Copper, PVC Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES DIR BUR

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Triads
20	7x28	BC - Bare Copper	36	12
22	7x30	BC - Bare Copper	1	

Conductor Count:	37
Total Number of Pairs:	N/A
Total Number of Triads:	1

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.0175 in
PVC - Polyvinyl Chloride	0.019 in

Color Chart

Number	Color
1	Black and Red and White and Numbered 1
2	Black and Red and White and Numbered 2
3	Black and Red and White and Numbered 3
4	Black and Red and White and Numbered 4
5	Black and Red and White and Numbered 5
6	Black and Red and White and Numbered 6
7	Black and Red and White and Numbered 7
8	Black and Red and White and Numbered 8
9	Black and Red and White and Numbered 9
10	Black and Red and White and Numbered 10
11	Black and Red and White and Numbered 11
12	Black and Red and White and Numbered 12
13	Orange

Color Chart 2

Number	Color
1	Black & White & Red and Numbered 1
2	Black & White & Red and Numbered 2
3	Black & White & Red and Numbered 3
4	Black & White & Red and Numbered 4
5	Black & White & Red and Numbered 5
6	Black & White & Red and Numbered 6
7	Black & White & Red and Numbered 7

8	Black & White & Red and Numbered 8
9	Black & White & Red and Numbered 9
10	Black & White & Red and Numbered 10
11	Black & White & Red and Numbered 11
12	Black & White & Red and Numbered 12
Communication Wire	Orange

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.771 in	0.063 in	Yes

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	26 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
30 pF/ft	55 pF/ft

Inductance

Nominal Inductance
0.19 µH/ft

Current

Max. Recommended Current [A]
3 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	319 lbs/1000ft
Max Recommended Pulling Tension:	636 lbs
Min Bend Radius/Minor Axis:	7.15 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 UL Loading
ICEA Flammability:	T-29-520
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
1085A 0105000	Black	612825106135	5,000 ft	C Z

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

History

Update and Revision:	Revision Number: 0.308 Revision Date: 09-10-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.