



**Product:** [1094A](#)

Inst, 8 Tri #18 Str BC, PVC-NYL Ins E1, IS/OS, Blk PVC Jkt, 600V TC-ER  
150V NPLF 90C Dry 75C Wet

[Request Sample](#)

## Product Description

UL Instrumentation, 8 Triad 18AWG (7x26) Bare Copper, PVC-NYL Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 150V NPLF 90C Dry 75C Wet SUN RES DIR BUR

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Triads
18	7x26	BC - Bare Copper	8

Conductor Count:	24
Total Number of Triads:	8

#### Insulation

Material	Nominal Diameter
PVC/Nylon - Polyvinyl Chloride + Nylon	0.088 in

#### Color Chart

Number	Color
1	Black and Red and White and Printed #1
2	Black and Red and White and Printed #2
3	Black and Red and White and Printed #3
4	Black and Red and White and Printed #4
5	Black and Red and White and Printed #5
6	Black and Red and White and Printed #6
7	Black and Red and White and Printed #7
8	Black and Red and White and Printed #8

#### Color Chart 2

Number	Color
1	Black & White & Red and Numbered 1
2	Black & White & Red and Numbered 2
3	Black & White & Red and Numbered 3
4	Black & White & Red and Numbered 4
5	Black & White & Red and Numbered 5
6	Black & White & Red and Numbered 6
7	Black & White & Red and Numbered 7
8	Black & White & Red and Numbered 8

#### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
------	----------	---------------------	--------------	--------------------	---------------	------------------------------

Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	18	7x26
------	-------------------------	-----------	------	--------------------	----	------

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.738 in	0.064 in	Yes

## Construction and Dimensions

#### Stranding

##### Twists

4.8 twist/ft

#### Cabling

##### Twists

1.32 twist/ft

## Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	7.11 Ohm/1000ft	4.22 Ohm/1000ft

#### Voltage

##### UL Voltage Rating

600 V RMS

150 V RMS (Type NPLF)

## Temperature Range

UL Temp Rating:	75°C Dry, 90°C Wet
Wet Temp Range:	-30°C To +75 °C
Dry Temp Range:	-30°C To +90 °C

## Mechanical Characteristics

Bulk Cable Weight:	311.5 lbs/1000ft
Max. Pull Tension:	672 lbs
Min. Bend Radius/Minor Axis:	7.5 in

## Standards

NEC/(UL) Compliance:	NPLF, TC-ER
Other Specification:	ICEA S-73-532, S-61-402

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1685 UL Loading
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

## Plenum/Non-Plenum

Plenum (Y/N): No

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
1094A 0105000	Black	Reel	5,000 ft	612825106364

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

## Product Notes

Notes: Triad groups are numbered for ease of identification. Alternate color coding available upon request.

## History

Update and Revision: Revision Number: 0.348 Revision Date: 05-26-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.