



**Product:** [10GB24D](#)

10GB Category 6A Cable, 4 Pair, U/UTP, LSZH Indoor CPR Dca

### Product Description

Category 6A Premise Horizontal Cable (625MHz), 4-Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Polyethylene Insulation, LSZH Jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Horizontal and building backbone cable; Support current and future Category 6A and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/patents">https://www.belden.com/patents</a> .

#### Construction Details

##### Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Solid	BC - Bare Copper	4

##### Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	1.2 mm (0.047 in)	White / Blue & Blue, White / Orange & Orange, White / Green & Green, White / Brown & Brown

##### Cable Core

Description	Separator
4 pairs twisted to cable core covered with a polyester foil	Center Member (Patented X-Spline®), EquiBlock™ Barrier Technology

##### Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	7.1 mm (0.28 in)

Overall Cable Diameter (Nominal):	7.1 mm (0.28 in)
-----------------------------------	------------------

#### Electrical Characteristics

##### Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

##### Delay

Max. Delay Skew	Nom. Velocity of Prop.
45 ns/100m	67%

##### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. PSANEXT [dB]	Min. PSAACRF [dB]	Min. TCL [dB]	Min. ELCTL [dB]
1	2.1 dB/100m	75.3	72.3	73.2	70.2	68	65.0	20	67.0	67	40	35
4	3.8 dB/100m	66.3	63.3	62.5	59.5	56	53.0	23	67.0	66.2	40	23
10	5.9 dB/100m	60.3	57.3	54.4	51.4	48	45.0	25	67.0	58.2	40	15
16	7.5 dB/100m	57.2	54.2	49.8	46.8	43.9	40.9	25	67.0	54.1	38	10.9

31.2	10.5 dB/100m	52.9	49.9	42.4	39.4	38.1	35.1	23.6	67.0	48.3	35.1	5.1
62.5	15 dB/100m	48.4	45.4	33.4	30.4	32.1	29.1	21.5	65.6	42.3	32	
100	19.1 dB/100m	45.3	42.3	26.2	23.2	28	25.0	20.1	62.5	38.2	30	
125	21.5 dB/100m	43.8	40.8	22.3	19.3	26.1	23.1	19.4	61.0	36.3	29	
200	27.6 dB/100m	40.8	37.8	13.2	10.2	22	19.0	18	58.0	32.2	27	
250	31.1 dB/100m	39.3	36.3	8.3	5.3	20	17.0	17.3	56.5	30.2	26	
300	34.3 dB/100m	38.1	35.1	3.9	0.9	18.5	15.5	17.3	55.3	28.7		
500	45.3 dB/100m	34.8	31.8	-10.4	-13.4	14	11.0	17.3	52.0	24.2		
625	51.2 dB/100m	33.4	30.4	-17.8	20.8	12.1	9.1	14.5	50.6	22.3		

#### Voltage

Voltage Rating
72 V DC

### Mechanical Characteristics

#### Temperature

Operating	Installation
-30°C to 60°C	0°C To +50°C

#### Bend Radius

Stationary Min.	Installation Min.
29 mm (1.1 in)	58 mm

Max. Pull Tension:	110 N (25 lbf)
Bulk Cable Weight:	50 kg/km

### Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Dca-s2,d2,a1
IEEE Compliance:	PoE: IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1
GENELEC Compliance:	EN 50173-1, Segregation class according EN50174-2 = b
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

### Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system.
--------	--

### History

Update and Revision:	Revision Number: 0.160 Revision Date: 01-13-2025
----------------------	--

### Part Numbers

#### Variants

Item #	Color	Putup Type	Length	EAN
10GB24D.10305	Black	Reel	305 m	8719605227218
10GB24D.06305	Blue	Reel	305 m	8719605227133
10GB24D.K6305	Blue	Reel	305 m	8719605227140
10GB24D.06500	Blue	Reel	500 m	8719605182098
10GB24D.08305	Gray	Reel	305 m	8719605227164
10GB24D.K8305	Gray	Reel	305 m	8719605227195
10GB24D.K5305	Green	Reel	305 m	8719605227201
10GB24D.07305	Purple	Reel	305 m	8719605227157
10GB24D.07500	Purple	Reel	500 m	8719605222985

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.