



Product: [10GX13](#) 

10GX Category 6A Enhanced Cable, 4 Pair, U/UTP, CMP

Product Description

10GX Category 6A Enhanced Premise Horizontal Cable (625MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet up to 10GBASE-T, HDBaseT, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White & Blue, White & Orange, White & Green, White & Brown

Bonded-Pair: No

Outer Jacket Material

Separator Material	Material	Material Trade Name	Nom. Diameter	Ripcord
Double H Cross-Web (Patented RoundFlex®)	PVC - Polyvinyl Chloride	Flamarrest®	0.295 in	Yes

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. DCR Unbalanced Between Pairs [%]	Max. Capacitance Unbalance	Nom. Mutual Capacitance
74 Ohm/km	3%	5%	50 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]	Typical Delay Skew
100 MHz	537.6 ns/100m	45 ns/100m	68%	35 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	73.3 dB	71.2 dB	68.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	67.0 dB	67.0 dB	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	64.3 dB	60.5 dB	56.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	67.0 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	59.8 dB	54.4 dB	50.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	61.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	58.3 dB	52.4 dB	48.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	59.2 dB	40.0 dB	15.0 dB
16 MHz	7.5 dB/100m	55.2 dB	47.8 dB	44.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	55.1 dB	40.0 dB	10.9 dB
20 MHz	8.4 dB/100m	53.8 dB	45.4 dB	42.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	53.2 dB	38.0 dB	9.0 dB
25 MHz	9.4 dB/100m	52.3 dB	43.0 dB	40.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	51.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	50.9 dB	40.4 dB	38.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	49.3 dB	35.1 dB	

62.5 MHz	15.0 dB/100m	46.4 dB	31.4 dB	32.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	66.6 dB	43.3 dB	32.0 dB	
100 MHz	19.1 dB/100m	43.3 dB	24.2 dB	28.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 10 Ohm	63.5 dB	39.2 dB	30.0 dB	
200 MHz	27.6 dB/100m	38.8 dB	11.2 dB	22.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 10 Ohm	59.0 dB	33.2 dB	27.0 dB	
250 MHz	31.1 dB/100m	37.3 dB	6.3 dB	20.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	57.5 dB	31.2 dB	26.0 dB	
300 MHz	34.3 dB/100m	36.1 dB	1.9 dB	19.3 dB	16.8 dB	100 ± 32 Ohm	100 ± 10 Ohm	56.3 dB	29.7 dB	25.2 dB	
350 MHz	37.2 dB/100m	35.1 dB		17.9 dB	16.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	55.3 dB	28.3 dB	24.6 dB	
400 MHz	40.1 dB/100m	34.3 dB		16.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	54.5 dB	27.2 dB	24.0 dB	
450 MHz	42.7 dB/100m	35.5 dB		15.7 dB	15.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	53.7 dB	26.1 dB	23.5 dB	
500 MHz	45.3 dB/100m	32.8 dB		14.8 dB	15.2 dB	100 ± 32 Ohm	100 ± 10 Ohm	53.0 dB	25.2 dB	23.0 dB	
550 MHz	47.7 dB/100m	32.2 dB		14.0 dB	14.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	52.4 dB	24.4 dB		
600 MHz	50.1 dB/100m	31.6 dB		13.2 dB	14.7 dB	100 ± 32 Ohm	100 ± 10 Ohm	51.8 dB	23.6 dB		
625 MHz	51.2 dB/100m	31.4 dB		12.9 dB	14.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	51.6 dB	23.3 dB		
750 MHz	56.7 dB/100m	30.2 dB		11.3 dB	14.0 dB			50.4 dB	21.7 dB		
860 MHz	61.2 dB/100m	29.3 dB		10.1 dB	13.6 dB			49.5 dB	20.5 dB		

Voltage

UL Voltage Rating
300 V (CMP), 300 V (CL3P)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation	Storage
105°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.25 in	3.0 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	43 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, FT6, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMP;CMP-LP (0.6A);CL3P-LP (0.6A)
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732-2013
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
Cenelec Compliance:	Segregation class according EN50174-2=a
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	Verified Channel/Category 6A

Part Number

Non-Plenum Number:	10GX12
--------------------	--------

Variants

Item #	Color	Putup Type	Length	UPC
10GX13 0101000	Black	Reel	1,000 ft	612825102274
10GX13 0101500	Black	Reel	1,500 ft	612825102281
10GX13 D151000	Blue	Reel	1,000 ft	612825102182
10GX13 D152500	Blue	Reel	2,500 ft	612825102199
10GX13 0081000	Gray	Reel	1,000 ft	612825102250

10GX13 0051000	Green	Reel	1,000 ft	612825102236
10GX13 0071000	Purple	Reel	1,000 ft	612825102243
10GX13 0091000	White	Reel	1,000 ft	612825102267
10GX13 0041000	Yellow	Reel	1,000 ft	612825102205
10GX13 0042500	Yellow	Reel	2,500 ft	612825102212
10GX13 0045000	Yellow	Reel	5,000 ft	612825102229

Product Notes

Notes: Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 625 MHz are for Engineering Information Only. 0.295" Cable Dimension per TIA 6@1 Equivalent Diameter. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.

History

Update and Revision: Revision Number: 0.472 Revision Date: 02-16-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.