



**Product:** [10GX44](#)

CAT6A 10GX Bonded-Pair, 4pr, UTP, LSZH Jkt

### Product Description

CAT6A (625MHz), 4-Bonded-Pair, U/UTP-unshielded, Zero Halogen, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, patented Double-H spline, ripcord, LSZH jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 10G Category 6A, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/patents">https://www.belden.com/patents</a> .

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
------------------	---

##### Insulation

Material
PO - Polyolefin

Bonded-Pair:	Yes
--------------	-----

##### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

##### Outer Shield

Material
No Shield

##### Outer Jacket

Material	Nominal Diameter	Separator Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.295 in	Double H Cross-Web (Patented RoundFlex®)

#### Electrical Characteristics

##### Conductor DCR

Max. DCR Unbalance	Nominal Conductor DCR
2 %	7.5 Ohm/1000ft

##### Capacitance

Nom.Mutual Capacitance
17 pF/ft

## Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
100 MHz	538 ns/100m	45 ns/100m	64%	35 ns/100m

## High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	75.3 dB	73.3 dB	73.2 dB	71.2 dB	70.8 dB	68.8 dB	20 dB	100 ± 15 Ohm	100 ± 15 Ohm	67 dB	67 dB	48 dB	43 dB
4 MHz	3.8 dB/100m	66.3 dB	64.3 dB	62.5 dB	60.5 dB	58.8 dB	56.8 dB	23 dB	100 ± 15 Ohm	100 ± 10.4 Ohm	67 dB	67 dB	48 dB	41 dB
8 MHz	5.3 dB/100m	61.8 dB	59.8 dB	56.4 dB	54.4 dB	52.7 dB	50.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 8 Ohm	67 dB	61.1 dB	48 dB	24.9 dB
10 MHz	5.9 dB/100m	60.3 dB	58.3 dB	54.4 dB	52.4 dB	50.8 dB	48.8 dB	25 dB	100 ± 15 Ohm	100 ± 7.3 Ohm	67 dB	59.2 dB	48 dB	23 dB
16 MHz	7.5 dB/100m	57.2 dB	55.2 dB	49.8 dB	47.8 dB	46.7 dB	44.7 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	67 dB	55.1 dB	46 dB	18.9 dB
20 MHz	8.4 dB/100m	55.8 dB	53.8 dB	47.4 dB	45.4 dB	44.8 dB	42.8 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	67 dB	53.2 dB	45 dB	17 dB
25 MHz	9.4 dB/100m	54.3 dB	52.3 dB	45 dB	43 dB	42.8 dB	40.8 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	67 dB	51.2 dB	44 dB	15 dB
31.25 MHz	10.5 dB/100m	52.9 dB	50.9 dB	42.4 dB	40.4 dB	40.9 dB	38.9 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	67 dB	49.3 dB	43.1 dB	
62.5 MHz	15 dB/100m	48.4 dB	46.4 dB	33.4 dB	31.4 dB	34.9 dB	32.9 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	66.6 dB	43.3 dB	40 dB	
100 MHz	19.1 dB/100m	45.3 dB	43.3 dB	26.2 dB	24.2 dB	30.8 dB	28.8 dB	25 dB	100 ± 15 Ohm	100 ± 5 Ohm	63.5 dB	39.2 dB	38 dB	
200 MHz	27.6 dB/100m	40.8 dB	38.8 dB	13.2 dB	11.2 dB	24.8 dB	22.8 dB	21 dB	100 ± 22 Ohm	100 ± 5 Ohm	59 dB	33.2 dB	35 dB	
250 MHz	31.1 dB/100m	39.3 dB	37.3 dB	8.3 dB	6.3 dB	22.8 dB	20.8 dB	20.5 dB	100 ± 32 Ohm	100 ± 5 Ohm	57.5 dB	31.2 dB	34 dB	
300 MHz	34.3 dB/100m	38.1 dB	36.1 dB	3.9 dB	1.9 dB	21.3 dB	19.3 dB	20.1 dB	100 ± 32 Ohm	100 ± 5 Ohm	56.3 dB	29.7 dB	33.2 dB	
350 MHz	37.2 dB/100m	37.1 dB	35.1 dB			19.9 dB	17.9 dB	19.8 dB	100 ± 32 Ohm	100 ± 5 Ohm	55.3 dB	28.3 dB	32.6 dB	
400 MHz	40.1 dB/100m	36.3 dB	34.3 dB			18.8 dB	16.8 dB	19.5 dB	100 ± 32 Ohm	100 ± 5 Ohm	54.5 dB	27.2 dB	32 dB	
450 MHz	42.7 dB/100m	35.5 dB	33.5 dB			17.7 dB	15.7 dB	18.9 dB	100 ± 32 Ohm	100 ± 5 Ohm	53.7 dB	26.1 dB	31.5 dB	
500 MHz	45.3 dB/100m	34.8 dB	32.8 dB			16.8 dB	14.8 dB	18.4 dB	100 ± 32 Ohm	100 ± 5 Ohm	53 dB	25.2 dB	31 dB	
550 MHz	47.7 dB/100m	34.2 dB	32.2 dB			16 dB	14 dB	18 dB	100 ± 32 Ohm	100 ± 5 Ohm	52.4 dB	24.4 dB		
600 MHz	50.1 dB/100m	33.6 dB	31.6 dB			15.2 dB	13.2 dB	17.6 dB	100 ± 32 Ohm	100 ± 5 Ohm	51.8 dB	23.6 dB		
625 MHz	51.2 dB/100m	33.4 dB	31.4 dB			14.9 dB	12.9 dB	17.4 dB	100 ± 32 Ohm	100 ± 5 Ohm	51.6 dB	23.3 dB		
750 MHz	56.7 dB/100m	32.2 dB	30.2 dB			13.3 dB	11.3 dB	16.5 dB			50.4 dB	21.7 dB		
860 MHz	61.2 dB/100m	31.3 dB	29.3 dB			12.1 dB	10.1 dB	15.8 dB			49.5 dB	20.5 dB		

Segregation class according EN50174-2:

a

## Voltage

UL Voltage Rating

300 V RMS

## Temperature Range

Operating Temperature Range: 0°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	40 lbs/1000ft
Max. Pull Tension:	45 lbs
Min. Bend Radius During Installation:	3.0 in
Min. Bend Radius/Minor Axis:	2 in

## Standards

CPR Euroclass:	Eca
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA/EIA 568 C.2 Category 6A

## Applicable Environmental and Other Programs

Environmental Space:	LSZH
----------------------	------

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

Non-Plenum Number:	10GX32
--------------------	--------

## Variants

Item #	Color	Put-Up Type	Length	UPC
10GX44 0061000	Blue, Light			612825102380
10GX44 0071000	Violet			612825102397
10GX44 0091000	White	Reel	1,000 ft	612825102403

## Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals. Third party channel verified to TIA/EIA-568-C.2, Category 6A. Category 6A. 0.295" cable dimension per TIA 6@1 equivalent diameter. Values above 625MHz are for Engineering Information Only.
--------	---

## History

Update and Revision:	Revision Number: 0.357 Revision Date: 12-19-2022
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.