



Part Number: 10GX53F

CAT6A (625MHz), 4 Unbonded Pairs, F/UTP-Foil Shielded, CMP

Product Description

CAT6A (625MHz), 4 Unbonded Pairs, F/UTP-Foil Shielded, Plenum-CMP, Premise Horizontal Cable, 23 AWG Solid Bare Copper Conductors, FEP Insulation, Patented EquiSpline™, Overall Foil Screen with Drain Wire, Ripcord, Flamarrest® Jacket

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	Premise Horizontal Cable, 10 Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, PoE, PoE+

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
FEP - Fluorinated Ethylene Propylene	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	26

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.275 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Max DCR Unbalanced Between Pairs [%]
82 Ohm/km	4 %	5 %

Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance

90 pF/100m	17 pF/ft
------------	----------

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	68 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCL [dB]
1 MHz	2.1 dB/100m	73.3 dB	71.2 dB	68.8 dB	20.0 dB	100 ± 15 Ohm	105 ± 10 Ohm	77.0 dB	77.0 dB	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	64.3 dB	60.5 dB	56.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	76.2 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	59.8 dB	54.4 dB	50.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	70.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	58.3 dB	52.4 dB	48.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	68.2 dB	40.0 dB	15.0 dB
16 MHz	7.5 dB/100m	55.2 dB	47.8 dB	44.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	64.1 dB	38.0 dB	10.9 dB
20 MHz	8.4 dB/100m	53.8 dB	45.4 dB	42.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	62.2 dB	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	52.3 dB	43.0 dB	40.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	77.0 dB	60.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	50.9 dB	40.4 dB	38.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 10 Ohm	77.0 dB	58.3 dB	35.1 dB	
62.5 MHz	15.0 dB/100m	46.4 dB	31.4 dB	32.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	77.0 dB	52.3 dB	32.0 dB	
100 MHz	19.1 dB/100m	43.3 dB	24.2 dB	28.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 10 Ohm	72.5 dB	48.2 dB	30.0 dB	
200 MHz	27.6 dB/100m	38.8 dB	11.2 dB	22.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 10 Ohm	68.5 dB	42.2 dB	27.0 dB	
250 MHz	31.1 dB/100m	37.3 dB	6.3 dB	20.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	66.5 dB	40.2 dB	26.0 dB	
300 MHz	34.3 dB/100m	36.1 dB	1.9 dB	19.3 dB	16.8 dB	100 ± 32 Ohm	100 ± 10 Ohm	65.3 dB	38.7 dB	25.2 dB	
350 MHz	37.2 dB/100m	35.1 dB		17.9 dB	16.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	64.3 dB	37.3 dB	24.6 dB	
400 MHz	40.1 dB/100m	34.3 dB		16.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	63.5 dB	36.2 dB	24.0 dB	
450 MHz	42.7 dB/100m	33.5 dB		15.7 dB	15.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.7 dB	35.1 dB	23.5 dB	
500 MHz	45.3 dB/100m	32.8 dB		14.8 dB	15.2 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.0 dB	34.2 dB	23.0 dB	
550 MHz	47.7 dB/100m	32.2 dB		14.0 dB	14.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.4 dB	34.4 dB		
600 MHz	50.1 dB/100m	31.6 dB		13.2 dB	14.7 dB	100 ± 32 Ohm	100 ± 10 Ohm	61.8 dB	33.6 dB		
625 MHz	51.2 dB/100m	31.4 dB		12.9 dB	14.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	61.6 dB	33.3 dB		
750 MHz	56.7 dB/100m	30.2 dB		11.3 dB	14.0 dB	100 ± 32 Ohm	100 ± 10 Ohm	60.4 dB	31.7 dB		
860 MHz	61.2 dB/100m	29.3 dB		10.1 dB	13.6 dB	100 ± 32 Ohm	100 ± 10 Ohm	59.5 dB	30.5 dB		

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	+5°C To +50°C
UL Temp Rating:	105°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	38 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.75 in
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class EA
CPR Euroclass:	Eca
Data Category:	Category 6A
ANSI Compliance:	S-116-732-2013 Category 6A, ANSI/NEMA WC-66 Category 6A
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6A
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Specification:	Verified Channel/Category 6A
Other Standards:	C(UL)US CMP 105C OR (UL) CMP-LP (0.7A) OR CL3P-LP (0.7A)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2014-03-27
CA Prop 65 (CJ for Wire & Cable):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262 Plenum (UL 910)
CSA Flammability:	FT6
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	10GX52F
--------------------	---------

Variants

Item #	Color	UPC
10GX53F 0101000	Black	612825377795
10GX53F D151000	Blue	612825377757
10GX53F 0081000	Gray	612825377771
10GX53F 0091000	White	612825377788
10GX53F 0041000	Yellow	612825377764

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Values above 625 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.202 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and

regulations based on their individual usage of the product.