



REPRESENTATIVE IMAGE

Product: [1115A](#)

Type JX Thermocouple, 1 Pr #16 Sol, FEP Ins Wht, Red, OS, Blk FEP Jkt, 300V PLTC CL2P 200C SUN RES

[Request Sample](#)

Product Description

Type JX Thermocouple, 1 Pair 16AWG (Solid) Iron+Constantan, FEP Insulation Wht, Red Color Code, Overall Beldfoil® Shield, Black FEP Outer Jacket, PLTC CL2P 200C SUN RES

Technical Specifications

Product Overview

| | |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Suitable Applications: | Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), Thermocouple, distributed control system (DCS), programmable logic controller (PLC) |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Construction Details

Conductor

| Element | Number of Element | AWG | Stranding | Material |
|---------|-------------------|-----|-----------|-------------------|
| Pair(s) | 1 | 16 | Solid | Iron & Constantan |

Insulation

| Element | Material | Thickness | Color Code |
|---------|--------------------------------------|-----------|-------------|
| Pair(s) | FEP - Fluorinated Ethylene Propylene | 0.010 in | White & Red |

Outer Shield Material

| Shield Type | Material | Coverage | Drainwire Type |
|-------------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100% | 18 AWG (7x26) TC |

Outer Jacket Material

| Material | Thickness | Nom. Diameter |
|--------------------------------------|-----------|---------------|
| FEP - Fluorinated Ethylene Propylene | 0.012 in | 0.170 in |

Cable Diameter (Nominal): 0.170 in

Electrical Characteristics

Electricals

| Element |
|---------|
| Pair(s) |

| | |
|-----------------------|------------------------------------------------------------------------|
| Table Notes: | Conductor DCR (Nom): 24 Ohm/1000ft (Iron), 121 Ohm/1000ft (Constantan) |
| Nom Outer Shield DCR: | 5.5 Ohm/1000ft |

Voltage

| UL Voltage Rating |
|----------------------------|
| 300 V (PLTC), 300 V (CL3P) |

Mechanical Characteristics

Temperature

| UL Rating | Operating |
|-----------|-----------------|
| 200°C | -70°C to +200°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 1.75 in | 1.7 in |

| | |
|--------------------|---------------|
| Max. Pull Tension: | 83 lbs |
| Bulk Cable Weight: | 30 lbs/1000ft |

Standards and Compliance

| | |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Environmental Suitability: | Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance |
| Flammability / Fire Resistance: | NFPA 262, UL 910 (Plenum), T-29-520 |
| NEC / UL Compliance: | Article 725, CL3P, PLTC |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |
| Other Standard Compliance(s): | ISA MC 96.1-1982 Type JX |

Product Notes

| | |
|--------|----------------------------------------------------------|
| Notes: | Constantan is a Hoskins Manufacturing Company trademark. |
|--------|----------------------------------------------------------|

History

| | |
|----------------------|--------------------------------------------------|
| Update and Revision: | Revision Number: 0.362 Revision Date: 02-19-2021 |
|----------------------|--------------------------------------------------|

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.