



**Product:** [1192A](#)

Microphone Cable, Star Quad, 4 C #24 Str BC, 92% TC Braid, PVC Jkt

**Product Description**

Microphone Cable, Star Quad, 4 Conductor 24 AWG (42 x 40) High Conductivity Bare Copper, PE Insulation, 92% Tinned Copper Braid Shield, PVC Jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	Microphone, Low Noise for high-EMI environments; Line level balanced analog audio
------------------------	---

**Construction Details**

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	24 AWG	42x40	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.016 in (0.41 mm)	0.056 in (1.4 mm)	Blue, White, Blue/White Stripe, White/Blue Stripe

Outer Shield

Shield Type	Material	Coverage	Notes
Braid	Tinned Copper (TC)	92%	Paper tape under braid

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.044 in (1.1 mm)	0.245 in (6.22 mm)

Overall Cable Diameter (Nominal):	0.245 in (6.22 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Conductor(s)	26.6 Ohm/1000ft	39.2 pF/ft (129 pF/m)	40 Ohm	66%	3.04 Amps per conductor @ 30°C

Voltage

Voltage Rating
100 V

**Mechanical Characteristics**

Temperature

Operating
-30°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension:	47.2 lbs (21.4 kg)
Bulk Cable Weight:	33 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Quad connection scheme: The two blue wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the two white wires (or remaining wires) are connected together to form the second conductor.
--------	---

History

Update and Revision:	Revision Number: 0.515 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1192A B59100	Black, Matte	Reel	100 ft	612825108191	
1192A B59500	Black, Matte	Reel	500 ft	612825108214	C
1192A B591000	Black, Matte	Reel	1,000 ft	612825108207	C
1192A B59N1000	Black, Matte	Reel w/Small Barrel	1,000 ft	612825108184	C
1192A G7X500	Blue, Matte	Reel	500 ft	612825108269	
1192A G7X1000	Blue, Matte	Reel	1,000 ft	612825108252	C
1192A U901000	Gray, Matte	Reel	1,000 ft	612825108283	C
1192A G7W1000	Green, Matte	Reel	1,000 ft	612825108245	C
1192A G7WN1000	Green, Matte	Reel w/Small Barrel	1,000 ft	612825108238	C
1192A G8C1000	Purple, Matte	Reel	1,000 ft	612825350118	
1192A G8CN1000	Purple, Matte	Reel w/Small Barrel	1,000 ft	612825350101	
1192A G7V1000	Red, Matte	Reel	1,000 ft	612825108221	C
1192A G8M1000	Yellow, Matte	Reel	1,000 ft	612825108276	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.