



Product: [10GX S/FTP LSZH PRE-TERM 6](#)

10GX Copper Pre-Term 6x S/FTP LSZH

Product Description

10GX Copper Pre-Term 6x S/FTP LSZH

Technical Specifications

Product Overview

Suitable Applications:	Horizontal and building cabling. Support current and future Category 6a and 6 applications, such as: 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	No. of Pairs
26	Stranded	4

Total Number of Pairs: 24

Insulation

Material
PE - Polyethylene (Foam)

Inner Shield

Element	Material
Shielded Pair(s)	Bi-Laminate (Alum+Poly)

Outer Shield

Material	Coverage [%]
Tinned Copper (TC)	30%

Outer Jacket

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.1 mm

Wiring Scheme: T568A/B-T568A/B

Packaging: Individually packaged in a paper based carton with test report inside

Connectors

Materials

Description	Material
Plug	Polycarbonate
Boot	LSZH
Front Connection	Phosphor Bronze with 50u inch Gold over Nickel Plating

Electrical Characteristics

Dielectric Strength:	2.5 kV DC
Current Rating:	1 A
Insulation Resistance:	5000 MOhm*km

Max Contact Resistance:	20 mOhm
-------------------------	---------

Temperature Range

Installation Temperature Range:	0°C To +50°C
Storage Temperature Range:	-20°C to +60°C
Operating Temperature Range:	-20°C to +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	25 mm
Plug /Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

ISO/IEC Compliance:	ISO/IEC 11801-1
Data Category:	Category 6A
TIA/EIA Compliance:	ISO/IEC 11801-1:2017; EN 50173-1 Amd 1 Category 6A; ANSI/TIA/EIA 568 C.2 Category 6A

Applicable Environmental and Other Programs

Environmental Space:	Indoor Rated (Not Riser or Plenum)
EU Directive 2002/95/EC (RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Related Part Numbers

Related Parts:	10GX Shielded Modular Jacks, 10GX shielded Patch Panels
----------------	---

Variants

Item #	Color	Length
CAE4100020MA06	Black	20 m
CAE4100005MA06	Black	5 m
CAE4100010MA06	Black	10 m
CAE4100015MA06	Black	15 m
CAE4100025MA06	Black	25 m
CAE4100030MA06	Black	30 m
CAE4100035MA06	Black	35 m
CAE4100045MA06	Black	40 m
CAE4100050MA06	Black	45 m
CAE4106005MA06	Blue	50 m
CAE4109005MA06	White	5 m

History

Update and Revision:	Revision Number: 0.94 Revision Date: 08-12-2024
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.