




**Product:** [1212F](#) 

Category 5E+ Cable, 4 Pair, F/UTP, CMR

### Product Description

Category 5E+ Premise Horizontal Cable (350MHz), 4 Pair, 24 AWG Solid Bare Copper Conductors, F/UTP - Foil Shielded, Riser-CMR, PVC Jacket

### Technical Specifications

#### Product Overview

|                        |  |
|------------------------|--|
| Suitable Applications: | Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE , Noisy Environments |
|------------------------|--|

#### Construction Details

##### Conductor

| AWG | Stranding | Material         | Number of Pairs |
|-----|-----------|------------------|-----------------|
| 24  | Solid     | BC - Bare Copper | 4               |

##### Insulation

| Material        | Color Code   |
|-----------------|--|
| PO - Polyolefin | White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown |
| Bonded-Pair:    | No   |

##### Outer Shield Material

| Type | Material                | Coverage | Drainwire Type   |
|------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100%     | 24 AWG (7x32) TC |

##### Outer Jacket Material

| Material                 | Nom. Diameter | Ripcord |
|--------------------------|---------------|---------|
| PVC - Polyvinyl Chloride | 0.260 in      | No      |

#### Electrical Characteristics

##### Electricals

| Max. Conductor DCR | Max. DCR Unbalance | Max. Capacitance Unbalance | Nom. Mutual Capacitance |
|--------------------|--------------------|----------------------------|-------------------------|
| 93.8 Ohm/km        | 3%                 | 330 pF/100m                | 15 pF/ft                |

##### Delay

| Frequency [MHz] | Max. Delay    | Max. Delay Skew | Nom. Velocity of Propagation (VP) [%] |
|-----------------|---------------|-----------------|---------------------------------------|
| 100 MHz         | 537.6 ns/100m | 45 ns/100m      | 70%                                   |

##### High Freq

| Frequency [MHz] | Max. Insertion Loss (Attenuation) | Min. NEXT [dB] | Min. PSNEXT [dB] | Min. ACR [dB] | Min. PSACR [dB] | Min. ACRF (ELFEXT) [dB] | Min. PSACRF (PSELFEXT) [dB] | Min. RL (Return Loss) [dB] | Max./Min. Input Impedance (unFitted) | Max./Min. Fitted Impedance |
|-----------------|-----------------------------------|----------------|------------------|---------------|-----------------|-------------------------|-----------------------------|----------------------------|--------------------------------------|----------------------------|
| 1 MHz           | 2.0 dB/100m                       | 70.3 dB        | 68.3 dB          | 70.3 dB       | 66.3 dB         | 67.8 dB                 | 64.8 dB                     | 20.0 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 4 MHz           | 4.0 dB/100m                       | 61.3 dB        | 59.3 dB          | 59.3 dB       | 55.3 dB         | 55.8 dB                 | 52.8 dB                     | 23.0 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 8 MHz           | 5.7 dB/100m                       | 56.8 dB        | 54.8 dB          | 53.1 dB       | 49.1 dB         | 49.7 dB                 | 46.7 dB                     | 24.5 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 10 MHz          | 6.4 dB/100m                       | 55.3 dB        | 53.3 dB          | 50.9 dB       | 46.9 dB         | 47.8 dB                 | 44.8 dB                     | 25.0 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 16 MHz          | 8.1 dB/100m                       | 52.2 dB        | 50.2 dB          | 46.1 dB       | 42.1 dB         | 43.7 dB                 | 40.7 dB                     | 25.0 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 20 MHz          | 9.1 dB/100m                       | 50.8 dB        | 48.8 dB          | 43.7 dB       | 39.7 dB         | 41.8 dB                 | 38.8 dB                     | 25.0 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |
| 25 MHz          | 10.2 dB/100m                      | 49.3 dB        | 47.3 dB          | 41.1 dB       | 37.1 dB         | 39.8 dB                 | 36.8 dB                     | 24.3 dB                    | 100 ± 15 Ohm                         | 100 ± 15 Ohm               |

|           |              |         |         |         |         |         |         |         |              |              |
|-----------|--------------|---------|---------|---------|---------|---------|---------|---------|--------------|--------------|
| 31.25 MHz | 11.4 dB/100m | 47.9 dB | 45.9 dB | 38.5 dB | 34.5 dB | 37.9 dB | 34.9 dB | 23.6 dB | 100 ± 15 Ohm | 100 ± 15 Ohm |
| 62.5 MHz  | 16.4 dB/100m | 43.4 dB | 41.4 dB | 29.0 dB | 25.0 dB | 31.9 dB | 28.9 dB | 21.5 dB | 100 ± 15 Ohm | 100 ± 15 Ohm |
| 100 MHz   | 21.0 dB/100m | 40.3 dB | 38.3 dB | 21.3 dB | 17.3 dB | 27.8 dB | 24.8 dB | 20.1 dB | 100 ± 15 Ohm | 100 ± 15 Ohm |
| 155 MHz   | 26.6 dB/100m | 37.4 dB | 35.4 dB | 12.8 dB | 8.9 dB  | 24.0 dB | 21.0 dB | 18.8 dB | 100 ± 22 Ohm | 100 ± 15 Ohm |
| 200 MHz   | 30.5 dB/100m | 35.8 dB | 33.8 dB | 7.3 dB  | 3.3 dB  | 21.8 dB | 18.8 dB | 18.0 dB | 100 ± 22 Ohm | 100 ± 15 Ohm |
| 250 MHz   | 34.4 dB/100m | 34.3 dB | 32.3 dB | 1.9 dB  |         | 19.8 dB | 16.8 dB | 17.3 dB | 100 ± 32 Ohm | 100 ± 15 Ohm |
| 300 MHz   | 38.0 dB/100m | 33.1 dB | 28.2 dB |         |         | 18.2 dB | 15.2 dB | 16.8 dB | 100 ± 32 Ohm | 100 ± 15 Ohm |
| 350 MHz   | 41.4 dB/100m | 32.1 dB | 27.2 dB |         |         | 16.9 dB | 13.9 dB | 16.3 dB | 100 ± 32 Ohm | 100 ± 15 Ohm |
| 400 MHz   | 44.6 dB/100m | 31.3 dB | 26.3 dB |         |         |         |         | 15.9 dB |              |              |
| 450 MHz   | 47.6 dB/100m | 30.5 dB | 25.6 dB |         |         |         |         | 15.5 dB |              |              |

## Voltage

|                          |
|--------------------------|
| <b>UL Voltage Rating</b> |
| 300 V (CMR)              |

## Mechanical Characteristics

### Temperature

| UL Rating | Operating      | Installation | Storage        |
|-----------|----------------|--------------|----------------|
| 75°C      | -20°C To +75°C | 0°C To +50°C | -20°C To +75°C |

### Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 2.25 in         | 2.75 in           |

|                    |               |
|--------------------|---------------|
| Max. Pull Tension: | 25 lbs        |
| Bulk Cable Weight: | 30 lbs/1000ft |

## Standards and Compliance

|                                 |  |
|---------------------------------|--|
| Environmental Suitability:      | Riser, Indoor  |
| Sustainability:                 | Product Lens™, Environmental Product Declaration (EPD) Available   |
| Flammability / Fire Resistance: | UL 1666 Riser, FT4, FT4, IEC 60332-1-2   |
| NEC / UL Compliance:            | 800, CMR   |
| CEC / C(UL) Compliance:         | CMR  |
| ICEA Compliance:                | S-90-661-2012  |
| IEEE Compliance:                | IEEE 802.3bt Type 1, Type 2, Type 3  |
| NEMA Compliance:                | NEMA WC-63.1   |
| Data Category:                  | Category 5e  |
| TIA/EIA Compliance:             | ANSI/TIA-568.2-D Category 5e   |
| CPR Euroclass:                  | Eca  |
| European Directive Compliance:  | EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16 |
| APAC Compliance:                | China RoHS II (GB/T 26572-2011)  |

## Part Number

|                |       |
|----------------|-------|
| Plenum Number: | 1213F |
|----------------|-------|

## Variants

| Item #         | Color  | Putup Type  | Length   | UPC          |
|----------------|--------|-------------|----------|--------------|
| 1212F 0101000  | Black  | Reel        | 1,000 ft | 612825108658 |
| 1212F 010A1000 | Black  | Reel-in-Box | 1,000 ft | 612825108641 |
| 1212F 006A500  | Blue   | Reel-in-Box | 500 ft   | 612825108573 |
| 1212F 0061000  | Blue   | Reel        | 1,000 ft | 612825108580 |
| 1212F 006A1000 | Blue   | Reel-in-Box | 1,000 ft | 612825108566 |
| 1212F 0081000  | Gray   | Reel        | 1,000 ft | 612825108603 |
| 1212F 008A1000 | Gray   | Reel-in-Box | 1,000 ft | 612825108597 |
| 1212F 0051000  | Green  | Reel        | 1,000 ft | 612825108559 |
| 1212F 005A1000 | Green  | Reel-in-Box | 1,000 ft | 612825108542 |
| 1212F 0031000  | Orange | Reel        | 1,000 ft | 612825108511 |
| 1212F 003A1000 | Orange | Reel-in-Box | 1,000 ft | 612825108504 |
| 1212F 0021000  | Red    | Reel        | 1,000 ft | 612825108498 |

|                |        |             |          |              |
|----------------|--------|-------------|----------|--------------|
| 1212F 002A1000 | Red    | Reel-in-Box | 1,000 ft | 612825108481 |
| 1212F 009A500  | White  | Reel-in-Box | 500 ft   | 612825108627 |
| 1212F 0091000  | White  | Reel        | 1,000 ft | 612825108634 |
| 1212F 009A1000 | White  | Reel-in-Box | 1,000 ft | 612825108610 |
| 1212F 0041000  | Yellow | Reel        | 1,000 ft | 612825108535 |
| 1212F 004A1000 | Yellow | Reel-in-Box | 1,000 ft | 612825108528 |

## Product Notes

|        |  |
|--------|--|
| Notes: | Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Shield is Bonded to Jacket Inner Wall for Electrical Stability. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0. |
|--------|--|

## History

|                      |  |
|----------------------|--|
| Update and Revision: | Revision Number: 0.410 Revision Date: 09-30-2020 |
|----------------------|--|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.