



**Product:** [10GX UHD PP 48 1U](#)



AX103264-10GX UHD Patch Panel, 48 Port, 1U

## Product Description

10GX Ultra-High Density Patch Panel, 48-port, 1U

## Technical Specifications

### Product Overview

Suitable Applications:	IBDN System 10GX, TIA Category 6A, ISO Class EA, 10GBASE-T
------------------------	--

### Physical Characteristics (Overall)

Height:	44.450 mm
Width:	482.600 mm
Depth:	34.544 mm
Port Count:	48 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	0.862 kg

### Connectors

#### Materials

Description	Material
Panel	Steel

### Construction and Dimensions

Max Capacity:	48 connectors
---------------	---------------

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

Tool Compatibility:	Gigaflex Connecting Tool (AX100749)
Plug /Jack Compatibility:	RJ45

### Standards

Data Category:	Category 6A
TIA/EIA Compliance:	Category 6A - TIA 568.B.2-10, ISO/IEC 11801:2002 Amendment 2

Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
------------------	-------------------------------------

## Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

## Flammability, LSOH, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

## Related Part Numbers

Related Parts:	10GX Modular Cords
----------------	--------------------

## Variants

Item #	Color	UPC
AX103264	Titanium	611589005821

## Product Notes

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 2 Velcro Straps; 2 cable management bars ;1 Installation Guide; 1 kit 10GX X-BAR
Notes:	For proper installation refer to Installation Guide PX104692 included with the product

## History

Update and Revision:	Revision Number: 0.264 Revision Date: 11-19-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.