



Product: [121702A](#)

CAT5e+ Horizontal Bonded-Pair, 2x4pr, UTP, PVC Jkt, CMR, Siamese

Product Description

CAT5e+ (350MHz), Siamese 2X4-Bonded-pairs, U/UTP-unshielded, Riser-CMR, Premise Horizontal cable, 24 AWG solid bare copper conductors, polyolefin insulation, ripcord, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc. exposure to rodent, crush, or cut through force,
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	8

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Inner Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.415 x 0.200 in	Yes

Armor

Armor Type & Material	Armor Thickness	Diameter Over Armor
AIA - Aluminum Interlock Armor	0.025 in (0.64 mm)	0.638 in (16.2 mm)

Outer Jacket

Separator	Material	Nom. Diameter
Polyester Tape	PVC - Polyvinyl Chloride	0.738 in (18.7 mm)

Overall Cable Diameter (Nominal):	0.738 in (18.7 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR
90 Ohm/km (27 Ohm/1000ft)

Delay

Nom. Velocity of Prop.
70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
1	2 dB/100m

4	4 dB/100m
8	5.7 dB/100m
10	6.4 dB/100m
16	8.1 dB/100m
20	9.2 dB/100m
25	10.3 dB/100m
31.25	11.6 dB/100m
62.5	16.8 dB/100m
100	21.7 dB/100m
155	27.7 dB/100m
200	32 dB/100m
250	36.4 dB/100m
300	40.5 dB/100m
310	41.3 dB/100m
350	44.3 dB/100m

Voltage

UL Voltage Rating
300 V (CMG)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Storage
60°C	-40°C To +60°C	-40°C To +60°C

Bend Radius

Stationary Min.
7.5 in (190 mm)

Max. Pull Tension:	200 lbs (91 kg)
Bulk Cable Weight:	182 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Indoor
NEC / UL Compliance:	CM
CEC / C(UL) Compliance:	CM
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals. U.S. Patents 5,606,151 and 5,734,126. Third party verified to TIA/EIA-568-B.2, Category 5e.
--------	--

History

Update and Revision:	Revision Number: 0.71 Revision Date: 05-31-2024
----------------------	---

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.