


Part Number: 1220B

Audio Snake Cable, #22-12pr, TC, Indiv. Shielded, CM



Product Description

Audio Snake Cable, 12-22 AWG tinned copper pairs, Datalene® insulation, individually shielded with Beldfoil® bonded to numbered/color-coded PVC jackets so both strip simultaneously, flexible PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	TC - Tinned Copper	0.03 in	12

Conductor Count:	24
Total Number of Pairs:	12

Insulation

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
FHDPE - Foamed High Density Polyethylene	Datalene®	0.06 in	0.015 in

Color Chart

Number	Color
1	Brown
2	Red
3	Yellow
4	Orange
5	Green
6	Blue
7	Purple
8	Gray
9	White
10	Black
11	Tan
12	Pink

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	0.030 in	22	7x30
						TC - Tinned Copper	

Inner Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.153 in	0.015 in

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.76 in	0.074 in	Yes
	0.76 in		

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
10.6 Ohm/1000ft	15 Ohm/1000ft	15 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
19 pF/ft	35 pF/ft

Inductance

Nominal Inductance
0.2 μ H/ft

Delay

Nominal Velocity of Propagation (VP) [%]
78 %

Current

Max. Recommended Current [A]
1.5 Amps per conductor @ 20°C

Voltage

Non-UL Voltage Rating	Voltage Rating [V]
150 V RMS	300 V RMS
300 V RMS	

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	271 lbs/1000ft
Max Recommended Pulling Tension:	328 lbs
Min Bend Radius/Minor Axis:	7.75 in

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Part Number

Plenum (Y/N):	No
---------------	----

Product Notes

Notes:	Datalene® insulation features include a low dielectric constant and a low dissipation factor for high-speed, low distortion data handling. Physical properties include good crush resistance and light weight. Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment.
--------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.