




**Product:** [1227A1](#) 

Category 3 Horizontal Cable, 2 Pair, U/UTP, CMR

## Product Description

Category 3 Premise Horizontal Cable (16MHz), 2 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Riser-CMR, PVC Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Ethernet 10BASE-T, Analog Phone, FAX
------------------------	--------------------------------------

### Construction Details

#### Conductor

AWG	Stranding	Material	Number of Pairs
24	Solid	BC - Bare Copper	2

#### Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange

Bonded-Pair:	No
--------------	----

#### Outer Jacket Material

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.173 in	No

### Electrical Characteristics

#### Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
93.8 Ohm/km	5%	90 pF/100m	15 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
16 MHz	543 ns/100m	45 ns/100m	70%

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. SRL (Structural Return Loss)	Max./Min. Fitted Impedance
1 MHz	2.6 dB/100m	41.0 dB	12.0 dB	100 ± 15 Ohm
4 MHz	5.6 dB/100m	32.0 dB	12.0 dB	100 ± 15 Ohm
8 MHz	8.5 dB/100m	27.0 dB	12.0 dB	100 ± 15 Ohm
10 MHz	9.7 dB/100m	26.0 dB	12.0 dB	100 ± 15 Ohm
16 MHz	13.1 dB/100m	23.0 dB	10.0 dB	100 ± 15 Ohm

#### Voltage

UL Voltage Rating
300 V (CMR)

### Mechanical Characteristics

## Temperature

UL Rating	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

## Bend Radius

Stationary Min.	Installation Min.
1.0 in	1.75 in

Max. Pull Tension:	15 lbs
Bulk Cable Weight:	12 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Riser, Indoor, Outdoor, Sunlight Resistance
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	UL 1666 Riser, FT4, FT4, IEC 60332-1-2
NEC / UL Compliance:	800, CMR
CEC / C(UL) Compliance:	CMR
ICEA Compliance:	S-90-661-2012
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 3
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 3
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Part Number

Plenum Number:	1243A2
----------------	--------

## Variants

Item #	Color	Putup Type	Length	UPC
1227A1 008U1000	Gray	UnReel	1,000 ft	612825109266
1227A1 Q5HU1000	White	UnReel	1,000 ft	612825109259

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage Markings.
--------	--

## History

Update and Revision:	Revision Number: 0.383 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.