



**Product:** [10GXW13](#)

10GXW (0.250") Category 6A Cable, 4 Pair, U/UTP, CMP

## Product Description

10GXW (0.250" Diameter) Category 6A Premise Horizontal Cable (500MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 10GBASE-T, Wi-Fi 6, Wi-Fi 5, In-Building Wireless, In-Building Small Cells, Mobile RAN, PoE++, PoE+, PoE, HDBaseT
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a> .

### Construction Details

#### Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

#### Insulation

Material	Color Code
FEP - Fluorinated Ethylene Propylene	White & Blue, White & Orange, White & Green, White & Brown

Bonded-Pair:	No
--------------	----

#### Outer Jacket Material

Separator Material	Material	Material Trade Name	Nom. Diameter	Ripcord
Center Member (Patented X-Spline®), EquiBlock™ Barrier Technology	PVC - Polyvinyl Chloride	Flamarrest®	0.250 in	Yes

### Electrical Characteristics

#### Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. DCR Unbalanced Between Pairs [%]	Max. Capacitance Unbalance	Nom. Mutual Capacitance
82 Ohm/km	3.0%	5.0%	45 pF/100m	17 pF/ft

#### Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Propagation (VP) [%]
537.6 ns/100m	45 ns/100m	69%

#### Voltage

<b>UL Voltage Rating</b>
300 V (CMP)

### Mechanical Characteristics

#### Temperature

UL Rating	Operating	Installation	Storage
105°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

#### Bend Radius

<b>Stationary Min.</b>
------------------------

1 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	37 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, FT6
NEC / UL Compliance:	800, CMP;CMP-LP (0.5A);CL3P-LP (0.5A)
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732-2013
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6A
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6A
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	Verified Channel/Category 6A

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

## History

Update and Revision:	Revision Number: 0.43 Revision Date: 09-30-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.