



Product: [123082F](#)

DeviceBus®, 2 Pr #15+18 Str TC, PVC+FPE Ins, IS+OA TC Brd, PVC Jkt, AIA Armor, PVC Jkt, Flexible, CMG PLTC

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 15+18AWG (65x33+65x36) Tinned Copper, PVC+Foam PE Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, PVC Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket, Flexible, CMG PLTC

Technical Specifications

Product Overview

Suitable Applications:	exposure to rodent, crush, or cut through force, harsh environment, ODVA device-level communication, used with CIP (common Industrial Protocol) for control, configuration, and data collection between devices, such as sensors and actuators, and higher level devices such as PLC, and PC in industrial automation, bus topology, etc.
------------------------	---

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Power Pair(s)	1	15 AWG	65x33	TC - Tinned Copper
Data Pair(s)	1	18 AWG	65x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code	Notes
Power Pair(s)	PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	Red & Black	
Data Pair(s)	PE - Polyethylene (Foam)	0.053 in (1.3 mm)	Blue & White	HDPE

Inner Shield

Element	Shield Type	Material	Coverage
Power Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%
Data Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Braid	Tinned Copper (TC)	65%	18 AWG (65x36) TC

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.480 in (12.2 mm)

Armor

Armor Type & Material
AIA - Aluminum Interlock Armor

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.053 in (1.3 mm)	0.779 in (19.8 mm)

Overall Cable Diameter (Nominal):	0.779 in (19.8 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Characteristic Impedance	Nom. Velocity of Prop.
Power Pair(s)		
Data Pair(s)	120 Ohm	75%

High Frequency

Element
Data Pair(s)

Voltage

UL Voltage Rating
300 V (CMG, PLTC)

Mechanical Characteristics

Temperature

UL Temperature
75°C

Standards and Compliance

Environmental Suitability:	Sunlight Resistance
NEC / UL Compliance:	Article 725, Article 800, CMG, PLTC
CEC / C(UL) Compliance:	CMG HLBCD

History

Update and Revision:	Revision Number: 0.50 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.