



REPRESENTATIVE IMAGE

Product: [123107A](#)

RS485, 2 Pr #22 Str TC, PE Ins, OS+TC Brd, PVC Jkt, AIA Armor, PVC Jkt, CM, PLTC

[Request Sample](#)

Product Description

RS-485, 2 Pair 22AWG (7x30) Tinned Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, PVC Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket, CM, PLTC

Technical Specifications

Product Overview

Suitable Applications:	exposure to rodent, crush, or cut through force, burial, serial communication (RS-485 standard) comprising of PLCs, VFDs, HMIs, motors, RTU, SCADA, etc. within noisy environments over long distance, outdoor such as solar, lighting, etc.
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.025 in (0.64 mm)	White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe	HDPE

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Braid	Tinned Copper (TC)	65%	

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.350 in (8.89 mm)

Armor

Armor Type & Material
AIA - Aluminum Interlock Armor

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.050 in (1.3 mm)	0.704 in (17.9 mm)

Cable Diameter (Nominal): 0.704 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.7 Ohm/1000ft	11 pF/ft	20.9 pF/ft	120 Ohm	78%	2.7 Amps per Conductor at 25°C
Nom. Outer Shield DCR:		2.95 Ohm/1000ft				

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss
Pair(s)	1 MHz	0.5 dB/100ft

Voltage

UL Voltage Rating
300 V (CM, PLTC)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
60°C	-40°C to +60°C	-20°C To +60°C

Table Notes: -40C

Bend Radius

Stationary Min.	Installation Min.
8.5 in (220 mm)	8.5 in

Max. Pull Tension: 200 lbs

Bulk Cable Weight: 172 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Sunlight Resistance
Flammability / Fire Resistance:	UL1685 UL Loading, FT4, 1202
NEC / UL Compliance:	Article 725, Article 800, CM, PLTC
CEC / C(UL) Compliance:	CMG HLBCD
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Revision Number: 0.368 Revision Date: 10-13-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.