



**Product:** [123107A](#)

RS485, 2 Pr #22 Str TC, PE Ins, OS+TC Brd, PVC Jkt, AIA Armor, PVC Jkt, CM, PLTC

[Request Sample](#)

### Product Description

RS-485, 2 Pair 22AWG (7x30) Tinned Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, PVC Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket, CM, PLTC

### Technical Specifications

#### Product Overview

Suitable Applications:	exposure to rodent, crush, or cut through force, burial, serial communication (RS-485 standard) comprising of PLCs, VFDs, HMIs, motors, RTU, SCADA, etc. within noisy environments over long distance, outdoor such as solar, lighting, etc.
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene (Foam)	0.025 in (0.64 mm)	0.079 in (2.0 mm)	White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe	HDPE

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Braid	Tinned Copper (TC)	65%	

##### Inner Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.053 in (1.3 mm)	0.350 in (8.89 mm)

##### Armor

Armor Type & Material	Armor Thickness	Armor Material Diameter
AIA - Aluminum Interlock Armor	0.025 in (0.64 mm)	0.560 in (14.2 mm)

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.045 in (1.1 mm)	0.690 in (17.5 mm)

Overall Cable Diameter (Nominal):	0.690 in (17.5 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.7 Ohm/1000ft	11 pF/ft (36 pF/m)	20.9 pF/ft	120 Ohm	78%	2.7 Amps per Conductor at 25°C

Nom. Outer Shield DCR:	2.95 Ohm/1000ft (9.68 Ohm/km)
------------------------	-------------------------------

##### High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	0.5 dB/100ft

#### Voltage

UL Voltage Rating
300 V

## Mechanical Characteristics

#### Temperature

UL Temperature	Operating	Installation
60°C	-40°C to +60°C	-20°C To +60°C

Table Notes: -40C

#### Bend Radius

Stationary Min.	Installation Min.
8.5 in (220 mm)	8.5 in (220 mm)

Max. Pull Tension: 200 lbs (91 kg)

Bulk Cable Weight: 172 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEEE 1202
NEC / UL Compliance:	Article 725, Article 800, CM, PLTC
CEC / C(UL) Compliance:	CMG, HLBCD
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision: Revision Number: 0.401 Revision Date: 04-30-2024

## Part Numbers

#### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
123107A 0105000	Black	Reel	5,000 ft	612825109631	C Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.