


**Product:** [1266A](#) 

Audio Cable, #22-2c, TC, O/A Foil, CM



## Product Description

Audio Cable, CM-Rated, 2-22 AWG stranded tinned copper conductors with polypropylene insulation, Beldfoil® shield, drain, PVC jacket

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	TC - Tinned Copper	0.0285 in	1

Conductor Count:	2
Total Number of Pairs:	1

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.0485 in	0.01 in

#### Color Chart

Number	Color
1	Black & Red

#### Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.024 in	24	7x32

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.143 in	0.02 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR
15 Ohm/1000ft	15 Ohm/1000ft		18 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	54 pF/ft

#### Inductance

Nominal Inductance
0.18 µH/ft

#### Impedance

**Nominal Characteristic Impedance**

55 Ohm

**Delay****Nominal Delay**   **Nominal Velocity of Propagation (VP) [%]**

1.5 ns/ft   66%

**Current****Max. Recommended Current [A]**

2.3 Amps per Conductor at 25°C

**Voltage****UL Voltage Rating**

300 V RMS

**Temperature Range**

UL Temp Rating:	60°C
Operating Temperature Range:	-20°C To +60°C

**Mechanical Characteristics**

Bulk Cable Weight:	14 lbs/1000ft
Max. Pull Tension:	25 lbs
Min. Bend Radius/Minor Axis:	1.5 in

**Standards**

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca

**Applicable Environmental and Other Programs**

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

**Suitability**

Suitability - Indoor:	Yes
-----------------------	-----

**Flammability, LSOH, Toxicity Testing**

UL Flammability:	UL1685 UL Loading
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Related Part Numbers****Variants**

Item #	Color	Put-Up Type	Length	UPC
1266A 0101000	Black	Reel	1,000 ft	612825110040
1266A 010U1000	Black	UnReel	1,000 ft	612825110033
1266A 006U1000	Blue, Light	UnReel	1,000 ft	612825109990
1266A 001U1000	Brown	UnReel	1,000 ft	612825109945
1266A 008U1000	Gray	UnReel	1,000 ft	612825110019
1266A 005U1000	Green, Dark	UnReel	1,000 ft	612825109983

1266A 003U1000	Orange	UnReel	1,000 ft	612825109969
1266A 002U1000	Red	UnReel	1,000 ft	612825109952
1266A 007U1000	Violet	UnReel	1,000 ft	612825110002
1266A 009U1000	White	UnReel	1,000 ft	612825110026
1266A 004U1000	Yellow	UnReel	1,000 ft	612825109976

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Unique design features lower capacitance and greater flexibility than standard audio pair constructions.
--------	--

## History

Update and Revision:	Revision Number: 0.339 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.